

Part number

CHI 48 LS



Bulkhead mounting housing, C-TYPE series,
with 1 lever, size 104.62, with metal cover

Product description

Product type	Bulkhead mounting housing
Series	C-TYPE
Closing type	With 1 lever
Size	Size 104.62
Cable entry	Without cable entry
Specification	With metal cover

Technical data

IP degree of protection	IP65
--------------------------------	------

Further technical details

Weight	649,50 g
Operating temperature range (min, max)	-40°C...+125°C

Material properties

Other materials	Lever: Stainless steel Gasket: NBR
Colour	RAL 7040 grey
RoHs conformity	Compliant
China RoHs - EFUP	E
REACH SVHC substances	No

Approvals / Standards

Certifications	CQC, DNV, BV
UL	ECBT2
cUL	ECBT8

General ordering information

EAN13 code	8015747018708
eCl@ss 8.1	27440202
ETIM 7.0	EC000437

Packaging Information


Packaging length	300,00 mm
Packaging height	160,00 mm
Packaging width	180,00 mm
Packaging weight	2,77 kg
Packaging volume	8,64 dm ³
Packaging description	Carton box
Packaging quantity	4 Pcs
Packaging EAN code	8015747018715
Sub-packaging weight	0,69 kg
Sub-packaging description	Plastic packaging
Sub-packaging quantity	1 Pcs
Sub-packaging EAN barcode	8015747018722

Part number

CHI 48 LS




Catalogue drawings



Catalogue drawings

CHI L - LS



Notes

Dimensions shown in mm are not binding and may be changed without notice.