


Data Sheet | Item Number: 216-264

Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

<https://www.wago.com/216-264>



Color: ■ black

Similar to illustration

Dimensions in mm

Connection Data		
Metric cross-section of the ferrule		1.5 mm ²
Strip length		14 ... 15 mm / 0.55 ... 0.59 inches
Cross-section (AWG) of ferrule		16 AWG

Physical data		
Total length (L)		18 mm
Wall thickness of crimp sleeve (W2)		0.15 mm
Wall thickness (plastic collar W1)		0.25 mm
Crimp length (length of sleeve L1)		12 mm
Inner diameter of plastic collar (D1)		3.5 mm
Diameter crimp sleeve inside (D2)		1.7 mm

Mechanical data		
Plastic collar		Standard collar
Suitable		2002 to 2006 Series

Material data		
Color		black
Fire load		0.001 MJ
Weight		0.2 g



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	1000 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918604291
Customs tariff number	85369010000

Product Classification	
UNSPSC	39121405
eCl@ss 10.0	27-40-02-01
eCl@ss 9.0	27-40-02-01
ETIM 9.0	EC000005
ETIM 10.0	EC000005
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance


Compliance Search

Environmental Product Compliance 216-264

↓

Documentation			
Bid Text			
216-264	19.02.2019	xml 2.80 KB	↓
216-264	11.09.2017	doc 23.50 KB	↓

Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com