

AS85049/29 (M38999/6) Straight Non-Environmental Strain Relief Backshell



AS85049

CONNECTOR DESIGNATOR:

F MIL-DTL-38999 Series I and II

TABLE III: Length Code

Code	Length ± .032 (0.8)
Standard	1.00 (25.4)
A	2.00 (50.8)
B	3.00 (76.2)
C	4.00 (101.6)

APPLICATION NOTES

- For complete dimensions see the applicable Military Specification.
- Metric dimensions (mm) are in parentheses.
- Cable Range is defined as the accommodation range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.





TABLE I: Shell Size and Clamp Size

Shell Size	Series I Ref.	Clamp Size* Min Max	A Thread Class 2B
08	09	01 02	.438 - 28 UNEF
10	11	01 03	.562 - 24 UNEF
12	13	02 04	.688 - 24 UNEF
14	15	02 05	.813 - 20 UNEF
16	17	02 06	.938 - 20 UNEF
18	19	03 07	1.063 - 18 UNEF
20	21	03 08	1.188 - 18 UNEF
22	23	03 09	1.313 - 18 UNEF
24	25	04 10	1.438 - 18 UNEF

*Clamp Size from Table II, AS85049/29 Specifications.

TABLE II: Clamp Size, Cable Range and Dimensions

Clamp Size	Cable Range Min Max	E Max
01	.062 (1.6) .125 (3.2)	.781 (19.8)
02	.125 (3.2) .250 (6.4)	.969 (24.6)
03	.250 (6.4) .375 (9.5)	1.062 (27.0)
04	.312 (7.9) .500 (12.7)	1.156 (29.4)
05	.437 (11.1) .625 (15.9)	1.250 (31.8)
06	.562 (14.3) .750 (19.1)	1.375 (34.9)
07	.687 (17.4) .875 (22.2)	1.500 (38.1)
08	.812 (20.6) 1.000 (25.4)	1.625 (41.3)
09	.937 (23.8) 1.125 (28.6)	1.750 (44.5)
10	1.062 (27.0) 1.250 (31.8)	1.875 (47.6)

Dimensions in inches (millimeters) and are subject to change without notice.

© 2013 Glenair, Inc.

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com B-55 E-Mail: sales@glenair.com