





MSDMXXX

Amphenol PCD SZ
ORIGINAL
PDF Format
18 Apr.17R&D

REV	ECN	DESCRIPTION	DATE	MODIFIED
A		PRE-RELEASE	2017.04.18	Gino Wu



HVIL PIN:
P/N:C200003644

TECHNICAL SPECIFICATIONS:

- SIGNAL CONNECTOR: C200003644
高压互锁信号连接器型号: C200003644
- RATED VOLTAGE/额定工作电压:
 - WITH FUSE/带保险丝: 最大1000V DC.
 - WITHOUT FUSE/不带保险丝: 最大1500V DC.
- RATED CURRENT/额定工作电流:
 - WITH FUSE/带保险丝: SELECTION BY FUSE/由保险丝规格而变动:
(160A、200A、250A、315A、350A、400A、450A、500A、550A、630A)
 - WITHOUT FUSE/不带保险丝: 300A MAX./最大300A;400APEAK/400A峰值
- OPERATE TEMPERATURE: -40°C TO +50°C/工作环境温度-40°C ~ +50°C
- HUMIDITY: 40%~70% (23±5°C)/相对湿度40%~70% (温度为23±5°C)
- IP CODE:IP67, IP6K9K(MATED)/插合后IP等级为IP67
- MATING & UN-MATING FORCE: <100N/插拔力小于100N
- DURABILITY >500 CYCLES/插拔次数大于500次

DIMENSIONS		TOLERANCES		PROJECTION	Amphenol Pcd Shenzhen					TITLE					
ANSI Y14.5M		.X ±1			ENGR					MSD XL PLUG					
UNITS: MM		.XX ±0.5			Gino Wu 2017.04.18										
CAD FILE		ANGLES ±0.5°													
ORIGINAL		THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN			CHKD					SIZE		DWG NO.		REV	
NOT FOR CUSTOMER DISTRIBUTION					APPD					A3		MSDXLMXXX		A	
										CODE:		SCALE 1:1		SHEET 1 OF 1	

MSDMXXX

MSDXLMXXX