

**Accessories**  
**DAE M12 PA long****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Pressure-compensation elements ensure good ventilation of the enclosure and prevent the build-up of condensation while maintaining the appropriate IP class of protection.

**General ordering data**

|            |                                                                                   |
|------------|-----------------------------------------------------------------------------------|
| Type       | DAE M12 PA long                                                                   |
| Order No.  | <a href="#">1868570000</a>                                                        |
| Version    | Accessories, Compensating element, M 12, 10 mm, IP 66, IP 68, IP 69K, Polyamide 6 |
| GTIN (EAN) | 4032248440429                                                                     |
| Qty.       | 10 pc(s).                                                                         |

## Accessories

### DAE M12 PA long

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Length     | 17.4 mm | Length (inches) | 0.685 inch |
| Net weight | 1.7 g   |                 |            |

### General information

|                                     |             |                                     |                                                                      |
|-------------------------------------|-------------|-------------------------------------|----------------------------------------------------------------------|
| AF size 1                           | 17 mm       | Air flow                            | 0.8 l/min at 0.1 bar $\Delta P$ , up to 7.6 l/min at 1bar $\Delta P$ |
| Cable gland                         | metric      | Colour code                         | RAL 9005                                                             |
| External thread                     | M 12        | Length of thread                    | 10 mm                                                                |
| Material                            | Polyamide 6 | O-Ring                              | NBR                                                                  |
| Operating temperature range, max.   | 105 °C      | Operating temperature range, min.   | -40 °C                                                               |
| Pitch of thread                     | 1.5 mm      | Protection degree with GWDR         | IP 66, IP 68, IP 69K                                                 |
| Torque for connecting adapter, max. | 0.5 Nm      | Torque for connecting adapter, min. | 0.5 Nm                                                               |
| UL 94 flammability rating           | V-2         | Wasser inlet point                  | > 1.5 bar                                                            |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000441    | ETIM 4.0   | EC000441    |
| ETIM 5.0   | EC000441    | ETIM 6.0   | EC000441    |
| UNSPSC     | 30-21-18-01 | eClass 6.2 | 27-14-91-09 |
| eClass 7.1 | 27-14-91-09 | eClass 8.1 | 27-14-91-09 |
| eClass 9.0 | 27-14-44-32 |            |             |

### Product information

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Descriptive text ordering data | Light grey version - RAL 7035 - on request |
|--------------------------------|--------------------------------------------|

### Approvals

Approvals




|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Accessories DAE M12 PA long

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Addresses worldwide

Let's connect.

## AE United Arab Emirates

Weidmüller Middle East FZE  
Warehouse Q3-79  
SAIF-Zone  
P.O. BOX 8591  
Sharjah  
Telephone number +971 65572723  
Fax number +971 65572724  
wme.info@weidmueller.com

## AO Angola

Please contact  
Phambili Interface  
South Africa

## AR Argentina

CPI SA  
Bauness 2660  
C1431DOF Buenos Aires  
Telephone number +54 11 4523 8008  
Fax number +54 11 4522 0546  
info@cpi.com.ar  
www.cpi.com.ar

## AT Austria

Weidmüller GmbH  
IZ NOE Süd Straße 2b, Obj  
M 59  
2355 Wiener Neudorf  
Telephone number +43 2236 67080  
Fax number +43 2236 6708-899  
office.at@weidmueller.com  
www.weidmueller.com

## AU Australia

Weidmüller Pty. Ltd.  
PO BOX 6944  
Huntingwood 2148  
Huntingwood Drive 43  
Huntingwood NSW 2148  
Telephone number +61 2 9671 9999  
Fax number +61 2 9671 9911  
info@weidmuller.com.au  
www.weidmuller.com.au

## AZ Azerbaijan

Representative Office  
Weidmüller Interface  
Demirchi Tower, 4th floor  
37, Khojali ave.  
AZ 1025 Baku  
Telephone number +994 12 488 80 36  
Fax number +994 12 488 80 37  
rashad.mahmudov@weidmueller.com

## BA Bosnia and Herzegovina

Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Serbia  
  
or  
  
BIG electric d.o.o  
Mladena Stojanovića 117A  
78000 Banja Luka  
Telephone number +387 51926277  
Fax number +387 51926277  
bigelectric@blic.net  
www.bigelectric.ba

## BE Belgium

Weidmüller Benelux B. V.  
Mechelsesteenweg 519 bus  
6 en 7  
1930 Nossegem  
Telephone number +32 2 752 40 70  
Fax number +32 2 751 36 06  
info@weidmueller.be  
www.weidmueller.be

## BG Bulgaria

Weid-Bul EOOD  
Bul. "Kliment Ohridski" 13  
1756 Sofia  
Telephone number +359 2 963 2560  
Fax number +359 2 963 1098  
sofia@weidbul.com  
www.weidbul.com

## BH Bahrain

Khayber Trading Company  
P.O Box 1976  
Manama  
Telephone number +973 720747  
Fax number +973 720331  
khayber@batelco.com.bh

## BR Brazil

Weidmüller Conexel do Brasil  
Conexões Elétricas Ltda.  
Av. Presidente Juscelino, 642  
- Piraporinha  
Diadema, São Paulo  
09950-370  
Telephone number +55 (11) 4366-9600  
Fax number +55 (11) 4362-1677  
vendas@weidmueller.com.br  
www.weidmueller.com.br

## BW Botswana

Please contact  
Phambili Interface  
South Africa

## BY Belarus

TECHNIKON Ltd.  
Nezavisimosti pr. 177-9  
220125 Minsk  
Telephone number +375 17 393-11-77  
Fax number +375 17 3930080  
wm@technikon.by

## CA Canada

W Interconnections Canada  
Inc.  
10 Spy Court  
Markham Ontario L3R 5H6  
Telephone number +1 (905) 475-1507 Ext. 9836  
Fax number +1 (905) 475-2798  
support@weidmuller.ca  
www.weidmuller.ca

## CG Congo

Please contact  
Phambili Interface  
South Africa

## CH Switzerland

Weidmüller Schweiz AG  
Rundbuckstraße 2  
8212 Neuhausen am  
Rheinfall SH  
Telephone number +41 52 674 07 07  
Fax number +41 52 674 07 08  
info@weidmueller.ch  
www.weidmueller.ch

## CL Chile

ATS- INTECH  
Maria Luisa Santander 0475  
Santiago  
Providencia 7500859  
Telephone number +56 2 341 1271  
Fax number +56 2 341 1275  
felipe@atsintech.com  
www.atsintech.com  
  
CPI CHILE LTDA  
Av. Presidente Frei Montalva  
6001, 47 complejo el cortijo  
Santiago - Conchalí  
Telephone number +562 963 8440  
Fax number +562 963 8440  
cpi@cpichile.cl  
www.cpichile.cl

## CN China

Weidmüller Interface  
(Shanghai) Co. Ltd.  
100 Yutong Road  
25 F. BM Intercontinental  
Business Center  
200070 Shanghai  
Telephone number +86 21-22195008  
Fax number +86 21-22195009  
customer.hotline@weidmueller.com.cn  
www.weidmueller.com.cn

## CO Colombia

Automatización Avanzada  
S. A.  
Carrera 97 No., 24 c - 23  
Bodega 4  
110911 Bogotá-D.C.  
Telephone number +57 (1) 547-8510  
Fax number +57 (1) 422-3044  
comercial@  
automatizacionavanzada.com  
www.  
automatizacionavanzada.com

## CR Costa Rica

ELVATRON S. A.  
la Uruca 400 Norte Banco  
Costa Rica  
San Jose Costa Rica  
Telephone number +506 2961-060  
Fax number +506 5200-609  
dirk.haase@elvatron.com  
www.elvatron.com

## CZ Czech Republic

Weidmüller s.r.o.  
Lomnického 5/1705  
140 00 Praha 4  
Telephone number +420 244 001 400  
Fax number +420 244 001 499  
office@weidmueller.cz  
www.weidmueller.cz

## DE Germany

Weidmüller GmbH & Co. KG  
Ohmstraße 9  
32758 Detmold  
Postfach 30 54  
32720 Detmold  
Telephone number +49 5231 1428-0  
Fax number +49 5231 14-292083  
weidmueller@weidmueller.de  
www.weidmueller.de

## DK Denmark

Weidmüller Danmark  
Vallensbækvej 18A  
2605 Brøndby  
Telephone number +45 27747800  
kundeservice@weidmueller.dk  
www.weidmueller.dk

## DZ Algeria

SARL INTER ELECTRIC  
1a Angles des Rues Okba Ibn  
Nafaa et Hassi Beida  
2300 Annaba  
Telephone number  
Fax number  
contact@inter-electric.com

## EC Ecuador

Elsystec S. A., Electricidad  
Sistemas y Tecnología  
Vasco de Contreras N35-251  
y Mañosa  
Quito - Pichincha  
Telephone number +593 22456510  
Fax number +593 22456755  
Elsystec@uio.satnet.net

## EE Estonia

Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Latvia  
  
or

Soots Interface OÜ  
Pärnu mnt 142  
11317 Tallinn  
Telephone number +372 609 6933  
Fax number  
info@sootsinterface.ee  
www.sootsinterface.ee

## EG Egypt

Standard Electric (OMEGA)  
1, Abdelhamid Badawy Street  
Heliopolis  
Cairo  
Telephone number +202 21805111  
Fax number +202 21805600  
stdelec@rite.com

## ES Spain

Weidmüller, S. A.  
Narcís Monturiol 11-13, Pol.  
Ind. Sudoeste  
8960 Sant Just  
Desvern - Barcelona  
Telephone number +34 934 803 386  
Fax number +34 933 718 055  
weidmuller@weidmuller.es  
www.weidmuller.es

## FI Finland

Weidmüller Suomi,  
Weidmüller Aktiebolagetin  
sivuliike  
Koy Plaza Vivace  
Äyrtie 8C  
FI 1510 Vantaa  
Telephone number +358 20 7351300  
Fax number +358 800 114 667  
asiakaspalvelu@weidmuller.fi  
www.weidmuller.fi

## FR France

Weidmüller E. U. R. L.  
12, Chaussée Jules César  
BP 263 Osny  
95523 Cergy-Pontoise Cedex  
Telephone number +33 1 34 24 55 00  
Fax number +33 1 34 24 55 01  
mail@weidmuller.fr

## GB Great Britain

Weidmüller Ltd.  
Klippon House  
Centurion Court Office Park,  
Meridian East, Meridian  
Business Park  
Leicester  
LE19 1TP  
Telephone number +44 116 282 3470  
Fax number +44 116 289 3582  
marketing@weidmuller.co.uk  
www.weidmuller.co.uk

## GE Georgia

Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

## GH Ghana

Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.

## GR Greece

G.A. Solutions  
Ippokratous 11 Metamorfosi  
144 52 Athen  
Telephone number +30 210 2823233  
Fax number +30 210 2823233  
info@weidmuller.gr  
www.weidmuller.gr

## GT Guatemala

Prestelectro, Prestegard  
Electro, S.A.  
Avenida Petapa 44-22,  
Zona 12  
Guatemala City  
Telephone number +502 2442-3346  
Fax number +502 2476-8945  
ventas@prestelectro.com

## HK Hong Kong

Weidmüller (Hong Kong)  
Limited Co. Ltd.  
Unit 1617, Metropolis Tower  
No. 10 Metropolis Drive,  
Hunghom, Kowloon  
Telephone number +852 3154 8088  
Fax number +852 31548099  
Info-hk@weidmueller.com.hk

## HR Croatia

ElektroPARTNER d.o.o.  
Slavonska avenija 24/6  
HR-10000 Zagreb  
Telephone number +385 (1) 6184 793  
Fax number +385 (1) 6184 795  
elektropartner@zg.t-com.hr  
www.elektropartner.hr

## HU Hungary

Weidmüller Kereskedelmi Kft.  
Budapest  
Gubacsi út 6.  
1097  
Telephone number +36 1 382 7700  
Fax number +36 1 382 7701  
info@weidmueller.hu  
www.weidmueller.hu

## ID Indonesia

PT. Nego Electrindo  
Ruko Mega Grosir Cempaka  
Mas Blok I No. 20 – 22  
Jakarta 10640  
Telephone number +62 21 42882255  
Fax number +62 21 42882266  
sales@negoelectrindo.co.id

## IE Ireland

Please contact  
Weidmüller Ltd.  
Great Britain

## IL Israel

A. U. Shay Ltd.  
23/25, Embar Street  
49222 Petach-Tikva  
P.O. Box 1 00 49  
49222 Petach-Tikva  
Telephone number +972 3-923-3601  
Fax number +972 3-923-4601  
shay@uriel-shay.com  
www.uriel-shay.com

ATEKA Ltd.  
4, Ha Tavor lane Industrial  
area Segula  
49691 Petach-Tikva  
P.O. Box 4710  
Petach-Tikva  
Telephone number +972 73-200-1311  
Fax number +972 3-924 4245  
marketing@ateka.co.il  
www.ateka.co.il

## IN India

Representative Office  
Weidmüller Electronics India  
Pvt. Ltd.  
12th Lane North Avenue, Opp  
Joggers Park,  
Kalyani Nagar, Pune  
411 006  
Telephone number +91 20-41290090  
wmi@weidmueller.in  
www.weidmueller.com

## IS Iceland

Samey Automation Center  
Lyngas 13  
210 Garoabær  
Telephone number +354 510 5200  
Fax number +354 5 10 5201  
Samey@samey.is  
www.samey.is

## IT Italy

Weidmüller S. r.l.  
Via Albert Einstein 4  
20092 Cinisello  
Balsamo Milano  
Telephone number +39 02 660681  
Fax number +39 02 6124945  
weidmuller@weidmuller.it  
www.weidmuller.it

## JM Jamaica

Please contact  
W Interconnections Inc.  
United States

## JO Jordan

Trans Jordan for Electro  
PO Box 33 06 07  
Amman  
Telephone number +962 6 533 2020  
Fax number +962 6 533 5800  
transjordan@batelco.jo



Let's connect.

You can find all Weidmüller addresses and your local contact on the internet at: [www.weidmueller.com/countries](http://www.weidmueller.com/countries)

Sales company

Representation abroad

without representation abroad

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p><b>JP Japan</b><br/>Nihon Weidmüller Co. Ltd.<br/>Sphere Tower Tennoz 2-2-8<br/>Higashi-Shinagawa,<br/>Shinagawa-ku<br/>Tokyo<br/>140-0002<br/>Telephone number +81 3<br/>6711 5300<br/>Fax number +81 3 6711<br/>5333<br/><a href="mailto:weidmullerjapan@weidmuller.co.jp">weidmullerjapan@weidmuller.co.jp</a><br/><a href="http://www.weidmuller.co.jp">www.weidmuller.co.jp</a></p>                                                                                                                                                                         | <p><b>MA Morocco</b><br/>Sofimed<br/>137, Bd Moulay Ismail Roches<br/>Noires<br/>20290 Casablanca<br/>Telephone number<br/>Fax number<br/><a href="mailto:contact@sofimedmaroc.com">contact@sofimedmaroc.com</a></p>                                                                                                                | <p><b>MY Malaysia</b><br/>Connect Plus Technology<br/>Sdn Bhd<br/>No. 43, Jalan PJS 11/22,<br/>Bandar Sunway<br/>46150 Petaling Jaya<br/>Selangor Darul Ehsan<br/>Telephone number +60 3<br/>5633 7363<br/>Fax number +60 3 5633<br/>6562<br/><a href="mailto:paul@cpotech.com.my">paul@cpotech.com.my</a><br/><a href="http://www.cpotech.com.my">www.cpotech.com.my</a></p>                                                                                                                                                                                                                     | <p><b>PH Philippines</b><br/>Enclosure Systems Specialists<br/>Inc.<br/>2276 Don Chino Roces<br/>Avenue Extension<br/>Room 103/105 Narra Building<br/>1231 Makati City<br/>Telephone number +63 2<br/>813 8580<br/>Fax number +63 2 813 8596<br/><a href="mailto:sales_encsys@pltdsl.net">sales_encsys@pltdsl.net</a><br/><a href="http://www.enclosuresystemsph.com">www.enclosuresystemsph.com</a></p>                                                                                                                                                                                             | <p><b>RS Serbia</b><br/>Representative Office<br/>Weidmüller Interface GmbH<br/>&amp; Co. KG<br/>Ustanicka 189, III sprat<br/>lokal 7a<br/>11050 Beograd<br/>Telephone number +381<br/>112885274<br/>Fax number +381<br/>112885274<br/><a href="mailto:zoran.rabrenovic@weidmueller.com">zoran.rabrenovic@weidmueller.com</a><br/><br/>TeLa Elektrik d.o.o.<br/>Ul.Dr Drage Ljočić 6<br/>Beograd<br/>Telephone number +381 11<br/>2772 415<br/>Fax number +381 11 2772<br/>850<br/><a href="mailto:office@tela.rs">office@tela.rs</a><br/><a href="http://www.tela.rs">www.tela.rs</a></p> |
| <p><b>KE Kenya</b><br/>Please contact<br/>our Representative Office<br/>Weidmüller Interface GmbH<br/>&amp; Co. KG<br/>South Africa.</p>                                                                                                                                                                                                                                                                                                                                                                                                                            | <p><b>MD Moldova</b><br/>BERHORD A &amp; D srl<br/>79/1, str. Milescu Spartaru<br/>MD-2075 Chisinau<br/>Moldova<br/>Telephone number +373 (22)<br/>815002<br/>Fax number +373 (22)<br/>815007<br/><a href="mailto:atuleanu@berhord.com">atuleanu@berhord.com</a><br/><a href="http://www.ad.berhord.com">www.ad.berhord.com</a></p> | <p><b>MZ Mozambique</b><br/>Please contact<br/>Phambili Interface<br/>South Africa</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | <p><b>PK Pakistan</b><br/>Automation Controls (Pak)<br/>Apartment No. 33 C III,<br/>Chenab Block, Allama Iqbal<br/>Town<br/>Lahore<br/>Telephone number +92 42<br/>37809948<br/>Fax number +92 42<br/>37809950<br/><a href="mailto:nadeem@acpak.com.pk">nadeem@acpak.com.pk</a><br/><a href="http://www.acpak.com.pk">www.acpak.com.pk</a></p>                                                                                                                                                                                                                                                       | <p><b>RU Russia</b><br/>Weidmüller Group<br/>7/10 Khlebozavodskiy<br/>Passage,<br/>Moskau<br/>115230<br/>Telephone number +7 495<br/>280 72 71<br/>Fax number +7 495 280<br/>72 71<br/><a href="mailto:Info@weidmueller.ru">Info@weidmueller.ru</a><br/><a href="http://www.weidmueller.ru">www.weidmueller.ru</a></p>                                                                                                                                                                                                                                                                     |
| <p><b>KG Kyrgyzstan</b><br/>Please contact<br/>our Representative Office<br/>Weidmüller Interface<br/>Azerbaijan.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                               | <p><b>ME Montenegro</b><br/>Please contact<br/>our Representative Office<br/>Weidmüller Interface GmbH<br/>&amp; Co. KG<br/>Serbia.</p>                                                                                                                                                                                             | <p><b>NA Namibia</b><br/>Please contact<br/>Phambili Interface<br/>South Africa</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               | <p><b>PL Poland</b><br/>Weidmüller Sp. z o. o.<br/>ul. Ogrodowa 58<br/>00-876 Warszawa<br/>Telephone number +48 22<br/>510 09 40<br/>Fax number +48 22 510<br/>09 41<br/><a href="mailto:biuro@weidmuller.com.pl">biuro@weidmuller.com.pl</a><br/><a href="http://www.weidmuller.pl">www.weidmuller.pl</a></p>                                                                                                                                                                                                                                                                                       | <p><b>SA Saudi Arabia</b><br/>Al Abdulkarim Holding Co.<br/>P.O. Box 4<br/>Dammam 31411<br/>Telephone number +966 3<br/>8337110<br/>Fax number +966 3<br/>8829547<br/>E-mail <a href="mailto:salehsak@akh.com.sa">salehsak@akh.com.sa</a><br/><a href="http://www.weidmueller.ae">www.weidmueller.ae</a></p>                                                                                                                                                                                                                                                                               |
| <p><b>KR Korea</b><br/>Weidmüller Korea Co. Ltd.<br/>9th floor<br/>429, Teheran-ro, Gangnam-Gu<br/>Seoul 135-721<br/>Telephone number +82<br/>2-516-0003<br/>Fax number +82 2-516-0090<br/><a href="mailto:info@weidmuller.co.kr">info@weidmuller.co.kr</a><br/><a href="http://www.weidmuller.co.kr">www.weidmuller.co.kr</a></p>                                                                                                                                                                                                                                  | <p><b>MG Madagascar</b><br/>Please contact<br/>Phambili Interface<br/>South Africa</p>                                                                                                                                                                                                                                              | <p><b>NL Netherlands</b><br/>Weidmüller Benelux B. V.<br/>Franciscusweg 221<br/>1216 SE Hilversum<br/>P.O. Box 1505<br/>1200 BM Hilversum<br/>Telephone number +31 35<br/>626 12 61<br/>Fax number +31 35 623<br/>20 44<br/><a href="mailto:info@weidmuller.nl">info@weidmuller.nl</a><br/><a href="http://www.weidmuller.nl">www.weidmuller.nl</a></p>                                                                                                                                                                                                                                           | <p><b>PR Puerto Rico</b><br/>Please contact<br/>W Interconnections Inc.<br/>United States</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        | <p><b>SE Sweden</b><br/>Weidmüller AB<br/>Axe Danielssons väg 271<br/>BOX 31025<br/>SE-200 49 Malmö<br/>Telephone number +46 77-<br/>143 00 44<br/>Fax number +46 40-37 48 60<br/><a href="mailto:info@weidmuller.se">info@weidmuller.se</a><br/><a href="http://www.weidmuller.se">www.weidmuller.se</a></p>                                                                                                                                                                                                                                                                              |
| <p><b>KW Kuwait</b><br/>Kana Controls General Trading<br/>&amp; Contracting Co. W. L. L.<br/>Al Rai Industrial Area, Plot<br/>28-30, St. 31<br/>13016 Safat<br/>B.P. 25593<br/>Telephone number +965<br/>4741373<br/>Fax number +965 4741537<br/><a href="mailto:info@kanacontrols.com">info@kanacontrols.com</a></p>                                                                                                                                                                                                                                               | <p><b>MK Macedonia</b><br/>Please contact<br/>our Representative Office<br/>Weidmüller Interface GmbH<br/>&amp; Co. KG<br/>Serbia</p>                                                                                                                                                                                               | <p><b>NO Norway</b><br/>Sivilingeniør J.F. Knudtzen AS<br/>Billingstadsløtta 97<br/>1396 Billingstad<br/>PO Box 160<br/>1378 Nesbru<br/>Telephone number +47 66<br/>98 33 50<br/>Fax number +47 66 98 09 55<br/><a href="mailto:firmapost@jfknuudtzen.no">firmapost@jfknuudtzen.no</a><br/><a href="http://www.jfknuudtzen.no">www.jfknuudtzen.no</a></p>                                                                                                                                                                                                                                         | <p><b>PT Portugal</b><br/>Weidmüller Sistemas de<br/>Interface S. A.<br/>Estrada Outeiro Polima, R.<br/>Augusto Dias da Silva, Lote<br/>B - Esc. 2<br/>São Domingos de Rana<br/>2785-515 Abóboda<br/>Telephone number +351 214<br/>459 191<br/>Fax number +351 214<br/>455 871<br/><a href="mailto:weidmuller@weidmuller.pt">weidmuller@weidmuller.pt</a><br/><a href="http://www.weidmuller.pt">www.weidmuller.pt</a></p>                                                                                                                                                                           | <p><b>SG Singapore</b><br/>Weidmüller Pte. Ltd.<br/>70 Bendemeer Road<br/># 04-03 Luzerne Building<br/>Singapore 339940<br/>Telephone number +65 6841<br/>5311<br/>Fax number +65 6841 5377<br/><a href="mailto:info@weidmuller.com.sg">info@weidmuller.com.sg</a><br/><a href="http://www.weidmuller.com.sg">www.weidmuller.com.sg</a></p>                                                                                                                                                                                                                                                |
| <p><b>KZ Kazakhstan</b><br/>Please contact<br/>Weidmüller Group<br/>Russia</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | <p><b>MN Mongolia</b><br/>Please contact<br/>our Representative Office<br/>Weidmüller Interface<br/>Azerbaijan.</p>                                                                                                                                                                                                                 | <p><b>NZ New Zealand</b><br/>Cuthbert S. Stewart Ltd.<br/>27 Te Puni Street<br/>Petone<br/>PO Box 38496<br/>Wellington Mail Centre 5054<br/>Telephone number (04) 568<br/>6156<br/>Fax number (09) 489 1752<br/><a href="mailto:cs@cutbertstewart.co.nz">cs@cutbertstewart.co.nz</a></p>                                                                                                                                                                                                                                                                                                          | <p><b>PY Paraguay</b><br/>Please contact<br/>CPI SA<br/>Argentina</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | <p><b>SI Slovenia</b><br/>Elektrospoji d. o. o.<br/>Stegne 27<br/>SI- 1000 Ljubljana<br/>Osrednjeslovenska<br/>Telephone number +386 1<br/>511 3810<br/>Fax number +386 1 511<br/>1604<br/><a href="mailto:info@elektrospoji.si">info@elektrospoji.si</a><br/><a href="http://www.elektrospoji.si">www.elektrospoji.si</a></p>                                                                                                                                                                                                                                                             |
| <p><b>LB Lebanon</b><br/>Progress Engineering &amp;<br/>Trading Enterprises<br/>Al Nahr Street<br/>Beirut 11-1111<br/>Telephone number +961 1<br/>444 664<br/>Fax number +961 1 561 880<br/><a href="mailto:progress@inco.com.lb">progress@inco.com.lb</a></p>                                                                                                                                                                                                                                                                                                      | <p><b>MT Malta</b><br/>E. S. S., Electrical Supplies &amp;<br/>Services Ltd.<br/>San Gwakklin Road<br/>Mriehel<br/><br/>Telephone number +356<br/>21255777<br/>Fax number +356 21255999<br/><a href="mailto:robert.agius@ess.com.mt">robert.agius@ess.com.mt</a></p>                                                                | <p><b>OM Oman</b><br/>DAN INTERNATIONAL LLC.<br/>Ghala St. 111<br/>BP 2901<br/>Seeb<br/>Telephone number +968<br/>5036 77<br/>Fax number +968 5037 55<br/><a href="mailto:yedu@danintl.com">yedu@danintl.com</a></p>                                                                                                                                                                                                                                                                                                                                                                              | <p><b>QA Qatar</b><br/>Doha Motors<br/>PO Box 145<br/><br/>Telephone number +974<br/>4651441<br/>Fax number +974 4654579<br/><a href="mailto:dmtctech@qatar.net.qa">dmtctech@qatar.net.qa</a><br/><a href="http://www.dohamotorsgroup.com/td.html">http://www.dohamotorsgroup.com/td.html</a><br/><br/>Petroleum Technology Co.<br/>W.L.L.<br/>PO Box 16069<br/>5th Floor Toyota tower<br/>Telephone number +974<br/>44419603<br/>Fax number +974 44419604<br/><a href="mailto:petrotec@qatar.net.qa">petrotec@qatar.net.qa</a><br/><a href="http://www.petrotec.com.qa">www.petrotec.com.qa</a></p> | <p><b>SK Slovakia</b><br/>ELEKTRIS s.r.o.<br/>Elektrárnská 1<br/>831 04 Bratislava<br/>Telephone number +421<br/>2/4920 0113<br/>Fax number +421 2/4920<br/>0119<br/><a href="mailto:bratislava@elektris.sk">bratislava@elektris.sk</a></p>                                                                                                                                                                                                                                                                                                                                                |
| <p><b>LT Lithuania</b><br/>Please contact<br/>our Representative Office<br/>Weidmüller Interface GmbH<br/>&amp; Co. KG<br/>Latvia<br/><br/>or<br/>ELEKTROS IRANGA<br/>Tinklų g. 29 a<br/>LT-5319 Panevėžys<br/>Telephone number +370 (45)<br/>582 828<br/>Fax number<br/><a href="mailto:info@eliranga.lt">info@eliranga.lt</a></p>                                                                                                                                                                                                                                 | <p><b>MU Mauritius</b><br/>Mubelo Electrical Ltd.<br/>Office 26, Gateway building,<br/>St Jean Road<br/>Quatre Bornes<br/>Mauritius<br/>Telephone number +230<br/>4670989<br/>Fax number +230 4654051<br/><a href="mailto:richard.mubelo@orange.mu">richard.mubelo@orange.mu</a></p>                                                | <p><b>PE Peru</b><br/>IMPEXINCA S.A.C.<br/>Calle Ortiz de Zevallos No.<br/>105, Urb. San Antonio<br/>18<br/>Lima, Miraflores<br/>Telephone number +51 1<br/>447 5608<br/><a href="mailto:info@impeixinca.pe">info@impeixinca.pe</a><br/><a href="http://www.impeixinca.pe">www.impeixinca.pe</a><br/><br/>J &amp; W CIA, S. A.<br/>Calle 6 Mz. D Lte. 23, Urb.<br/>Ind. Grimanesa<br/>01<br/>Callao<br/>Telephone number +51 1<br/>572 2539<br/>Fax number +51 1 572 0152<br/><a href="mailto:contacto@jwcia.com">contacto@jwcia.com</a><br/><a href="http://www.jwcia.com">www.jwcia.com</a></p> | <p><b>RO Romania</b><br/>Representative Office<br/>Weidmüller Interface GmbH<br/>&amp; Co. KG<br/>Ionescu Crum Street, No.<br/>1, 1st Tower, 1st Floor,<br/>Office 4<br/>500446 Brasov - Brasov<br/>Business Park<br/>Telephone number +40 (268)<br/>446 222<br/>Fax number +40 (262)<br/>205 410<br/><a href="mailto:claudiu.totea@weidmueller.com">claudiu.totea@weidmueller.com</a><br/><a href="http://www.weidmueller.com">www.weidmueller.com</a></p>                                                                                                                                          | <p><b>SE Sweden</b><br/>Weidmüller AB<br/>Axe Danielssons väg 271<br/>BOX 31025<br/>SE-200 49 Malmö<br/>Telephone number +46 77-<br/>143 00 44<br/>Fax number +46 40-37 48 60<br/><a href="mailto:info@weidmuller.se">info@weidmuller.se</a><br/><a href="http://www.weidmuller.se">www.weidmuller.se</a></p>                                                                                                                                                                                                                                                                              |
| <p><b>LU Luxembourg</b><br/>Please contact<br/>Weidmüller Benelux B. V.<br/>Netherlands</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | <p><b>MW Malawi</b><br/>Please contact<br/>our Representative Office<br/>Weidmüller Interface GmbH<br/>&amp; Co. KG<br/>South Africa.</p>                                                                                                                                                                                           | <p><b>RU Russia</b><br/>Weidmüller Group<br/>7/10 Khlebozavodskiy<br/>Passage,<br/>Moskau<br/>115230<br/>Telephone number +7 495<br/>280 72 71<br/>Fax number +7 495 280<br/>72 71<br/><a href="mailto:Info@weidmueller.ru">Info@weidmueller.ru</a><br/><a href="http://www.weidmueller.ru">www.weidmueller.ru</a></p>                                                                                                                                                                                                                                                                            | <p><b>SA Saudi Arabia</b><br/>Al Abdulkarim Holding Co.<br/>P.O. Box 4<br/>Dammam 31411<br/>Telephone number +966 3<br/>8337110<br/>Fax number +966 3<br/>8829547<br/>E-mail <a href="mailto:salehsak@akh.com.sa">salehsak@akh.com.sa</a><br/><a href="http://www.weidmueller.ae">www.weidmueller.ae</a></p>                                                                                                                                                                                                                                                                                         | <p><b>SG Singapore</b><br/>Weidmüller Pte. Ltd.<br/>70 Bendemeer Road<br/># 04-03 Luzerne Building<br/>Singapore 339940<br/>Telephone number +65 6841<br/>5311<br/>Fax number +65 6841 5377<br/><a href="mailto:info@weidmuller.com.sg">info@weidmuller.com.sg</a><br/><a href="http://www.weidmuller.com.sg">www.weidmuller.com.sg</a></p>                                                                                                                                                                                                                                                |
| <p><b>LV Latvia</b><br/>SIA Abi4<br/>Daugavgrivas 31b<br/>Rīga, LV-1007<br/>Telephone number +371 674<br/>70999<br/>Fax number +371 676<br/>24562<br/><a href="mailto:abi_4@tvnet.lv">abi_4@tvnet.lv</a><br/><br/>Representative Office<br/>Weidmüller Interface GmbH<br/>&amp; Co. KG<br/>Udens str. 12-118<br/>Rīga, LV-1007<br/>Telephone number +371<br/>29254766<br/>Fax number +371 674<br/>65637<br/><a href="mailto:ilgonis.rudaks@weidmueller.com">ilgonis.rudaks@weidmueller.com</a><br/><a href="http://www.weidmueller.com">www.weidmueller.com</a></p> | <p><b>MX Mexico</b><br/>W Interconnections S. A.<br/>DE C. V.<br/>Blvd. Hermanos Serdán 698,<br/>Col. San Rafael Oriente<br/>72029 Puebla<br/>Telephone number +52 (222)<br/>268 6227<br/>Fax number +52 (222) 286<br/>6242<br/><a href="mailto:clientes@weidmuller.com.mx">clientes@weidmuller.com.mx</a></p>                      | <p><b>OM Oman</b><br/>DAN INTERNATIONAL LLC.<br/>Ghala St. 111<br/>BP 2901<br/>Seeb<br/>Telephone number +968<br/>5036 77<br/>Fax number +968 5037 55<br/><a href="mailto:yedu@danintl.com">yedu@danintl.com</a></p>                                                                                                                                                                                                                                                                                                                                                                              | <p><b>QA Qatar</b><br/>Doha Motors<br/>PO Box 145<br/><br/>Telephone number +974<br/>4651441<br/>Fax number +974 4654579<br/><a href="mailto:dmtctech@qatar.net.qa">dmtctech@qatar.net.qa</a><br/><a href="http://www.dohamotorsgroup.com/td.html">http://www.dohamotorsgroup.com/td.html</a><br/><br/>Petroleum Technology Co.<br/>W.L.L.<br/>PO Box 16069<br/>5th Floor Toyota tower<br/>Telephone number +974<br/>44419603<br/>Fax number +974 44419604<br/><a href="mailto:petrotec@qatar.net.qa">petrotec@qatar.net.qa</a><br/><a href="http://www.petrotec.com.qa">www.petrotec.com.qa</a></p> | <p><b>SK Slovakia</b><br/>ELEKTRIS s.r.o.<br/>Elektrárnská 1<br/>831 04 Bratislava<br/>Telephone number +421<br/>2/4920 0113<br/>Fax number +421 2/4920<br/>0119<br/><a href="mailto:bratislava@elektris.sk">bratislava@elektris.sk</a></p>                                                                                                                                                                                                                                                                                                                                                |

# Addresses worldwide

Let's connect.

**SV El Salvador**  
Prestegard Electro  
11 Avenida Norte No. 240  
Edificio Salazar No. 2  
San Salvador  
Telephone number +503  
2271 1690  
Fax number +503 2221  
3851  
prestegard@navegante.com.sv

**SY Syria**  
Please contact  
Weidmüller Middle East FZE  
United Arab Emirates

**SZ Swaziland**  
Please contact  
Phambili Interface  
South Africa

**TH Thailand**  
Pisanu Engineering Co. Ltd.  
Kwang Dingaeng, Khet  
Dingaeng  
800/2 Soi Trakulsuk, Asoke-  
dindaeng Road  
Dindaeng, Bangkok  
10400  
Telephone number +66 2  
248 2896  
Fax number +662 105 6301  
ecsales@pisanu.co.th  
www.pisanu.co.th

Representative Office  
Weidmüller Pte. Ltd.  
37/F, Sathorn Square Building  
98 North Sathorn Road  
Bangkok, Silom Bangrak  
10500  
Telephone number +66 2  
105 6300  
Fax number +66 2 642 9220  
info@weidmuller.com.sg

**TJ Tajikistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

**TM Turkmenistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

**TN Tunisia**  
Please contact  
Weidmüller E. U. R. L.  
France

**TR Turkey**  
Weidmüller Elektronik Ticaret  
Ltd. Sirketi  
Kavacak Mah. Orhan Veli Kanik  
Caddesi 9/1  
34810 Beykoz / Istanbul  
Telephone number +90 (216)  
537 10 70  
Fax number +90 (216) 537  
10 77  
info@weidmuller.com.tr  
www.weidmuller.com.tr

**TW Taiwan**  
Weidmüller (Hong Kong)  
Limited  
No. 3, Lane 89, ChungYang  
N. Rd  
24148 SanChuang City,  
Taipei  
Telephone number +886 921  
949 751  
roy.lin@weidmueller.com.hk

**TZ Tanzania**  
Please contact  
our Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
South Africa.

**UA Ukraine**  
LLC WM UKRAINE  
Levanevskogo str. 6  
Kiev  
3058  
Telephone number +38 044  
490 32 48  
Fax number  
info@wm-ua.com.ua  
wm-ua.com.ua/

Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
Z, office 303  
7-D, Zdolbunivska str.  
Kiev, 2081  
Telephone number  
(mobile) +38 050 440 25 24  
info.ua@weidmueller.com

**US United States**  
W Interconnections Inc.  
821 Southlake Boulevard  
Richmond Virginia 23236  
Telephone number +1 (804)  
794-2877  
Fax number +1 (804) 379-  
2593  
info@weidmuller.com  
www.weidmuller.com

**UY Uruguay**  
REWO Uruguay S. A.  
AV. Bolivia 2001Esq  
Rocafuerte  
11300 Carrasco Montevideo  
Telephone number +598  
2604 8439  
Fax number +598 2604  
8439  
rewo@rewoouruguay.com.uy

**UZ Republic of Uzbekistan**  
Please contact  
our Representative Office  
Weidmüller Interface  
Azerbaijan.

**VE Venezuela**  
Somerinca C. A.  
Corazon de Jesus - 3ra  
Transversal con calle el  
Carmen- Los Dos Caminos  
Caracas 1070-A  
Telephone number +58  
2 122352748  
Fax number +58  
2122399341  
klocmoeller@cantv.net  
www.somerinca.com

**VN Vietnam**  
AUMI Industrial Equipment &  
Automation Company Limited  
E1, La Thanh Hotel  
218 Doi Can Street  
Lieu Giai Ward, Ba Dinh  
District  
Hanoi City  
Telephone number +84 4  
37628601  
Fax number +84 4  
62661391  
aumi@aumi.com.vn  
www.aumi.com.vn

Representative Office  
Weidmüller Pte. Ltd.  
Level 16 Saigon Tower  
Building  
29 Le Duan Street  
District 1  
Ho Chi Minh  
Telephone number +848  
3520 7717  
Fax number +848 3520  
7604  
info@weidmuller.com.sg

**ZA South Africa**  
Phambili Interface  
PO Box 193  
1609 Johannesburg, Edenvale  
5 Bundo Road, Sebenza  
1610 Johannesburg  
Telephone number +27 (11)  
4521930  
Fax number  
info@weidmuller.co.za  
www.weidmuller.co.za

Representative Office  
Weidmüller Interface GmbH  
& Co. KG  
210 Amarand  
Avenue, Pegasus Building  
181 Pretoria, waterkloof Glen  
ext 2 -  
Telephone number +27 12  
003 2906  
Fax number +27 (11)  
4526455  
Jacques.Vosloo@weidmueller.  
com  
www.weidmueller.com

**ZM Zambia**  
Please contact  
Phambili Interface  
South Africa

**ZW Zimbabwe**  
Please contact  
Phambili Interface  
South Africa