


- NOTES:
- 1. TAIL TYPE-FPC GOLD PLATED.
 - 2. PART IS ROHS COMPLIANT.
 - 3. DIMENSIONS IN PARENTHESIS ARE FOR REFERENCE ONLY.
 - 4. SENSOR SPECIFICATION PER QAD 19-1 (CURRENT REVISION).





REVISIONS					
ITEM REV	DWG REV	ECO	DESCRIPTION	DWN	DATE
A	1	-	INITIAL RELEASE.	JL	2-8-12
B	1	-	CHANGED OCA THICKNESS FROM 0.13mm TO 0.25mm	JL	5-22-12
C	1	0462	UPDATED TO CURRENT STANDARDS	WPD	11-13-13

SIDE VIEW

FRONT VIEW

J1	
PIN	FUNCTION
1	NC
2	SHIELD
3	Y1
4	Y2
5	Y3
6	Y4
7	Y5
8	Y6
9	Y7
10	Y8
11	Y9
12	Y10
13	Y11
14	Y12
15	SHIELD
16	NC
17	NC
18	NC
19	NC
20	NC
21	NC
22	NC
23	NC
24	NC

J2	
PIN	FUNCTION
1	NC
2	NC
3	NC
4	NC
5	NC
6	NC
7	NC
8	NC
9	SHIELD
10	X1
11	X2
12	X3
13	X4
14	X5
15	X6
16	X7
17	X8
18	X9
19	X10
20	X11
21	X12
22	X13
23	X14
24	X15
25	X16
26	X17
27	X18
28	X19
29	X20
30	SHIELD



Controlled
ENGINEERING / GRAPHICS

Signed by: Cassandra Ostrowski
Dated: 12-03-13



1016 North Lincoln Avenue, Pittsburgh, PA 15233
1.800.366.1904 • 412.322.9900 • Fax: 412.322.9958
e-mail: sales@dawar.com • www.dawar.com

THIS **CONFIDENTIAL** DOCUMENT IS THE PROPERTY OF DAWAR TECHNOLOGIES, INC. AND SHALL NOT BE COPIED, REPRODUCED, DISCLOSED, AND/OR USED AS THE BASIS FOR MANUFACTURING OR SALE WITHOUT PERMISSION OF A DULY AUTHORIZED REPRESENTATIVE OF DAWAR TECHNOLOGIES, INC.

DAWAR PART NO.
PCAP_7.0W-00001

DESCRIPTION
7.0"W PROJECTED CAPACITIVE TOUCHSCREEN (STANDARD PRODUCT)

ITEM/DRAWING NO.
DW00004-C

UNIT
MM [INCH]

TOLERANCE
±0.25 [0.010] UNLESS SPECIFIED

SHEET
1 OF 1

DRAWN BY
BILL DORFNER

DWG REV
1

DATE
11-13-13