

# Mobile Rack M28SACB

[Products](#) ▶ [Accessories](#) ▶ [Mobile Rack](#) ▶ [ [M28SACB](#) ]



Front View



Rear View

## Key Features

1. 8x 2.5" Hot-swap SAS3/SATA3 HDDs
2. Overheat LED and Alarm
3. Drive Activity / Failure LED
4. 2x 5.25" Drive Bay Enclosure
5. 2x Mini SAS HDD Connectors
6. 4cm Cooling Fan 12.5K RPM 16 CFM

## Available Colors

Black



## Downloads

Manual



## Specifications

Specifications	
<b>Dimensions</b>	<ul style="list-style-type: none"> <li>5.75" x 3.35" x 7.38" (146x85x187 mm)</li> <li>10.0" x 8.0" x 13.5" (package)</li> </ul>
<b>Gross Weight</b>	<ul style="list-style-type: none"> <li>4.8 lbs (2.18 kg) - with package</li> <li>3.2 lbs (1.44 kg) - Mobile rack only</li> </ul>
<b>Available Color</b>	<ul style="list-style-type: none"> <li>Black (CSE-M28SACB)</li> </ul>
<b>Occupancy</b>	<ul style="list-style-type: none"> <li>2x 5.25" Drive Bays</li> </ul>
<b>Capacity</b>	<ul style="list-style-type: none"> <li>8x 2.5" Hot-swap SAS3/SATA3 HDD trays</li> </ul>
<b>Cooling Subsystem</b>	<ul style="list-style-type: none"> <li>40mm x 28mm Cooling Fan, 12.5K RPM, 16CFM (FAN-0061L4)</li> </ul>
<b>Configuration</b>	<ul style="list-style-type: none"> <li>Direct attached</li> </ul>
<b>System Monitoring</b>	<ul style="list-style-type: none"> <li>Overheat LED and Alarm</li> <li>Drive Activity LED and Failure LED</li> </ul>

Compatibility	
<b>Chassis</b>	<ul style="list-style-type: none"> <li>SC842 Series</li> <li>SC835 Series</li> <li>SC743, SC745, SC747, SC748 Series</li> </ul>

Standard Parts List			
	Part Number	Qty	Description
Mobile Rack	CSE-M28SACB	1	SAS3 Mobile Rack CSE-M28SACB with fan
Drive Trays	MCP-220-00090-0B	8	Black gen 3.5 hot swap 2.5" HDD tray
Backplane	BPN-SAS3-I28A	1	SAS3 BPN - 8x2.5" SSD/HDD hotswap drive bays for CSE-M28SAC chassis,overheat indicator,SGPIO support SES2 mngrt,2 mini-SAS HD connector(SFF-8643),1 fan connector with fan fail detection
Cooling Fan	FAN-0061L4	1	40X28mm 4-PIN PWM Fan

Optional Parts List			
	Part Number	Qty	Description
Cables	CBL-SAST-0531	-	Mini-SAS HD to Mini-SAS HD 80cm,30AWG,12Gb/s
	CBL-SAST-0532	-	Mini-SAS HD to Mini-SAS HD 50cm,30AWG,12Gb/s
	CBL-SAST-0507-01	-	Mini-SAS to Mini-SAS HD 80cm w/ SB, 30AWG
	CBL-SAST-0508-01	-	Internal Mini-SAS to Mini-SAS HD 50cm w/ SB, 30AWG

[Terms & Conditions](#) | [Privacy](#) | [Investor Relations](#) | [Jobs](#) | [Site Map](#)

[SuperServer®](#) | [Motherboard](#) | [Chassis](#) | [Rack Cabinet](#) | [SuperBlade®](#) | [Embedded](#) | [Networking](#) | [Storage](#) | [Accessories](#) | [AMD Solution](#) | [Power Supplies](#)

Copyright © 2018 Super Micro Computer, Inc.

Information in this document is subject to change without notice.

Other products and companies referred to herein are trademarks or registered trademarks of their respective companies or mark holders.