



Product Locator

Product List

[Product Locator](#)[Web Specials](#)[Single Board Computers](#)[Graphics Processing Solutions/GPGPU](#)[COM Express](#)[VPX](#)[Gigabit Ethernet Solutions](#)[10G Ethernet Solutions](#)[SMARC Carrier Boards](#)[M.2](#)[Mini PCIe](#)[Rugged Tablets](#)[Custom Boards](#)[Embedded Systems](#)[Power Supplies](#)[Cellular/Satellite M2M](#)[FPGA](#)[Digital I/O](#)[Analog I/O](#)[Qseven Carrier Boards](#)[Storage Solutions](#)[Ethernet-to-serial](#)[Wireless Radio Modems](#)[CAN Controllers](#)[Synchronous Serial](#)[PC/104](#)[PC/104-Plus](#)[PCI/104-Express](#)[PCI-104](#)[CompactPCI](#)[PCI Express](#)[PCI](#)[ISA](#)[FeaturePak](#)[USB-to-serial](#)[Development Tools](#)[Cables & I/O Boxes](#)[Industrial Temp. Boards](#)[Conformal Coating](#)

Product Search Results

Displaying page 2 of 3

[Previous](#)[Next](#)

Part Number: BNG009-01
Product Name: Blue Heat/Net RS-232
Bus Type: Ethernet
Interface: RS-232
Ports: 2 ports

Cables: [CB006](#)

Max Baud: 230400 bps
Features: This Blue Heat/Net bundle includes: One BNG009 Blue Heat/Net 2 port adapter; one CBG006 6 foot CAT5 RJ-45 cable; and one MSG003 power supply for United States and Canada. RoHS compliant.

**BNG009-01**[product homepage](#)

Part Number: BNG009-02
Product Name: Blue Heat/Net RS-232
Bus Type: Ethernet
Interface: RS-232
Ports: 2 ports

Cables: [CBG006](#)

Max Baud: 230400 bps
Features: This Blue Heat/Net bundle includes: One BNG009 Blue Heat/Net 2 port adapter; one CBG006 6 foot CAT5 RJ-45 cable; and one MSG004 power supply for United Kingdom. RoHS Compliant.

**BNG009-02**[product homepage](#)

Part Number: BNG009-03
Product Name: Blue Heat/Net RS-232
Bus Type: Ethernet
Interface: RS-232
Ports: 2 ports

Cables: [CB006](#)

Max Baud: 230400 bps
Features: This Blue Heat/Net bundle includes: One BNG009 Blue Heat/Net 2 port adapter; one CBG006 6 foot CAT5 RJ-45 cable; and one MSG005 power supply for European Union. RoHS compliant.

**BNG009-03**[product homepage](#)

Part Number: BNG009-04
Product Name: Blue Heat/Net RS-232
Bus Type: Ethernet
Interface: RS-232
Ports: 2 ports

Cables: [CBG006](#)

Max Baud: 230400 bps
Features: This Blue Heat/Net bundle includes: One BNG009 Blue Heat/Net 2 port adapter; one CBG006 6 foot CAT5 RJ-45 cable; and one MSG007 universal power supply with line cord. RoHS Compliant.

**BNG009-04**[product homepage](#)

Part Number: BNG009-05
Product Name: Blue Heat/Net RS-232
Bus Type: Ethernet
Interface: RS-232
Ports: 2 ports



Cables:	CBG006
Max Baud:	230400 bps
Features:	This Blue Heat/Net bundle includes: One BNG009 Blue Heat/Net 2 port adapter; one CBG006 6 foot CAT5 RJ-45 cable. Includes Power over Ethernet and additional 36-56VDC input with screw down terminal connector. RoHS Compliant.

BNG009-05

[product homepage](#)

Part Number:	BNG010
Product Name:	Blue Heat/Net RS-232/422/485
Bus Type:	Ethernet
Interface:	RS-232/422/485
Ports:	2 ports
Cables:	No Cable
Max Baud:	230400 / 460800 bps (232/485)
Features:	This Blue Heat/Net is software configurable for RS-232/422/485. RoHS compliant.



BNG010

[product homepage](#)

Part Number:	BNG010-01
Product Name:	Blue Heat/Net RS-232/422/485
Bus Type:	Ethernet
Interface:	RS-232/422/485
Ports:	2 ports
Cables:	CB006
Max Baud:	230400 / 460800 bps (232/485)
Features:	This Blue Heat/Net bundle includes: One BNG010 Blue Heat/Net 2 port adapter; one CBG006 6 foot CAT5 RJ-45 cable; and one MS003 power supply for United States and Canada. RoHS compliant.



BNG010-01

[product homepage](#)

Part Number:	BNG010-02
Product Name:	Blue Heat/Net RS-232/422/485
Bus Type:	Ethernet
Interface:	RS-232/422/485
Ports:	2 ports
Cables:	CBG006
Max Baud:	230400 / 460800 bps (232/485)
Features:	This Blue Heat/Net bundle includes: One BNG010 Blue Heat/Net 2 port adapter, one CBG006 6 foot CAT5 RJ-45 cable and one MSG004 power supply for United Kingdom. RoHS Compliant.



BNG010-02

[product homepage](#)

Part Number:	BNG010-03
Product Name:	Blue Heat/Net RS-232/422/485
Bus Type:	Ethernet
Interface:	RS-232/422/485
Ports:	2 ports
Cables:	CBG006
Max Baud:	230400 / 460800 bps (232/485)
Features:	This Blue Heat/Net bundle includes: One BNG010 Blue Heat/Net 2 port adapter; one CBG006 6 foot CAT5 RJ-45 cable; one MSG005 power supply for European Union. RoHS Compliant.



BNG010-03

[product homepage](#)

Part Number:	BNG010-04
Product Name:	Blue Heat/Net RS-232/422/485
Bus Type:	Ethernet
Interface:	RS-232/422/485
Ports:	2 ports
Cables:	CBG006



BNG010-04

Max Baud:	230400 / 460800 bps (232/485)	product homepage
Features:	This Blue Heat/Net bundle includes: One BNG010 Blue Heat/Net 2 port adapter, one CBG006 6 foot CAT5 RJ-45 cable and one MSG007 universal power supply with line cord. RoHS Compliant.	