


BGA Heat Sink - High Performance maxiFLOW/superGRIP-Low-Profile



**Image above is for illustration purpose only.*

ATS Part#:	ATS-X51230K-C1-R0
Description:	23.00 x 23.00 x 14.50 mm BGA Heat Sink - High Performance maxiFLOW/superGRIP-Low-Profile
Heat Sink Type:	maxiFLOW
Heat Sink Attachment:	superGRIP
Equivalent Part Number:	N/A

Features & Benefits

- Requires minimal space around the component's perimeter; ideal for densely populated PCBs
- Allows the heat sink to be detached and reattached without damaging the component or the PCB, an important feature in the event a PCB may need to be reworked
- Strong, uniform attachment force helps achieve maximum performance from phase-change TIMs
- Eliminates the need to drill mounting holes in the PCB
- Assembly comes standard with a high performance maxiFLOW™ heat sink, which maximizes convection (air) cooling. Please refer to the superGRIP™ Keep-Out Guidelines and superGRIP™ Installation/Removal Guide for further details
- Comes standard with clean break, reworkable, Chomerics T-766 phase change material
- Designed for standard height components, from 1.5 to 2.9 mm

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	6.6 °C/W	5.4 °C/W	4.7 °C/W	4.2 °C/W	3.9 °C/W	3.6 °C/W	3.4 °C/W
	Ducted Flow	5.1	N/A	N/A	N/A	N/A	N/A	N/A

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	23.00 mm	23.00 mm	14.50 mm	41.54 mm	T766	Black Anodized
Notes: • Dimension A and B refer to component size. • Dimension C is the heat sink height from the bottom of the base to the top of the fin field. • Thermal performance data are provided for reference only. Actual performance may vary by application. • ATS reserves the right to update or change its products without notice to improve the design or performance. • ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant. • Contact ATS to learn about custom options available.						

**Image above is for illustration purpose only.*

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA

