Part Number : 1300950245
Product Description : Medium Duty Wire Mesh Slack Grip Cable, Split Lace, Double Weave, Offset Eye, Medium Mesh Length 0.508m (20.00"), Approximate Break Strength 3311.22kg (7300 lbs)
Series Number : 130095
Status : Obsolete
Product Category : Cable Grips
Engineering Part Number : 36125



Documents and Resources

Drawings

1300950245_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Medium Duty Wire Mesh Slack Grip Cable, Split Lace, Double Weave, Offset Eye, Medium Mesh Length 0.508m (20.00"), Approximate Break Strength 3311.22kg (7300 lbs)
Product Name	Medium Duty
Type	Pulling Grip
UPC	78678836125

Agency

CSA	LR32159

Physical

Approximate Break Strength	3311.22kg (7300 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	50.80-63.25mm (2.000-2.490")
Color - Grommet	N/A
Eye Type	Offset
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.508m (20.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Obsolete

Downloaded from Arrow.com.