
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

| RUGGEDIZED BACKSHELLS & ADAPTERS



✔ Active

TE CONNECTIVITY (TE)

BNX21AU90-1812AX

Raychem | Band Strap Backshells

BNX21AU90-1812AX
TE Internal Number: EF3509-000

Not EU RoHS Compliant
Not EU ELV Compliant

Cable Diameter Range 9.5 – 15.2 mm [.375 – .6 in]

Material Aluminum

Adapter Plating Material Zinc Cobalt over Electroless Nickel

Adapter Angle 90

Style Band Adapter

3D PDF

DOCUMENTATION

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Downloaded from Arrow.com.

Catalog Pages/Data Sheets

5-1654025-5_sec6_Adapters

PDF

English

Product Specifications

Product Specification

General Harness Repair Manual

PDF

English

General Information Package For BNDXXA (Band Strap) Adapters

PDF

English

Adapter Finish Specifications

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Product Type Features

Adapter Angle 90
Style Band Adapter
Termination Device Type Band Strap
Connector Shell Size 18
Accessory Type Band

Body Features

Color Olive Drab
Material Aluminum
Adapter Plating Material Zinc Cobalt over Electroless Nickel
TE Adapter Code 21
Adapter Entry Size 12

Termination Features

Overbraid Termination Band

Dimensions

Cable Diameter Range 9.5 – 15.2 mm [.375 – .6 in]
Cable Entry Diameter .2 – 19.1 mm [.01 – .75 in]

Usage Conditions

Operating Temperature Range -65 – 175 °C [-85 – 347 °F]
Salt Spray Resistance (Hr) 48

Downloaded from Arrow.com.

PRODUCT COMPLIANCE


Statement of Compliance

Statement of Compliance
PDF

Compatible Products

> Contact Product Support


Also in the Series | Band Strap Backshells



Ruggedized Backshells & Adapters (578)



Screened Backshells & Adapters (114)



Unscreened Backshells & Adapters (27)

Downloaded from Arrow.com.