
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -.- .
© COPYRIGHT – By – ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	REVISED PER ECO-18-004690	27MAR2018	RS	DR
	3	REVISED PER ECO-18-015080	24SEP2018	RS	DR
	A	REVISED PER ECO-18-016423	17OCT2018	RS	DR




AMP
WIRE RANGE

4 AWG
SOLID OR STRANDED

1 STAMP AMP 4* APPROX AS SHOWN





100	LOOSE PIECE	1958536-1
QTY	PACKAGE TYPE	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	
PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX

VOLTAGE RATING: NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE, 16.8-26.7mm²[33,100-52,600] CIR MILS SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± 0.127[.005]
4 PLC ± –
ANGLES ± –

MATERIAL COPPER PER ASTM B-152 ANNEALED

FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545

DWN	RAVI S	23MAY2017
CHK	ROHDE DANIEL	23MAY2017
APVD	ROHDE DANIEL	23MAY2017
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

TE Connectivity

NAME TERMINAL, RING TONGUE, BENT 90DEG, SOLISTRAND,™ 4 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1958536	—

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV A

1958536

1471-9 (1/15)

Downloaded from Arrow.com.