1674502-2 Product Details



Active

View 3D PDF

MTIS (MT Interconnection System)

REC ASSY 2P 0.8MT CONN

1674502-2

TE Internal Number: 1674502-2

Product Highlights View All

- Connector
- Connector Assembly
- Connector Style = Receptacle
- Contact Type = Socket
- 2 Positions

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Type	Connector
Connector Type	Connector Assembly
Color	Natural
Keyed	No
Mating Connector Lock	Without

Mechanical Attachment

Mounting Ears	Without

Dimensions

Insulation Diameter (mm [in])	0.39 [.015]

Body Features

Wire Range (Stranded) (mm² [AWG])	0.014² [36]
Daisy Chain	Without

Contact Features

Contact Type	Socket
Contact Plating, Mating Area, Material	Tin
Contact Base Material	Copper Alloy

Housing Features

Connector Style	Receptacle
Centerline (mm [in])	0.80 [0.031]
Housing Material	Thermoplastic

Configuration Features

Number of Positions	2
Number of Rows	Single

Industry Standards

RoHS/ELV Compliance ?	RoHS compliant, ELV compliant
Lead Free Solder Processes ?	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Applies To	Wire/Cable

Packaging Features

Packaging Method	Loose Piece

Other

Brand	AMP

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

[-] Feedback

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.