Products

- Clocks »
- **Crystals & Crystal Oscillators** »
  - ASSP XO
  - HiFlex XO
  - SSXO
  - **XO**
    - **Standard XO Part Quotes**
    - Custom XO Quotes
  - VCXO
  - TCXO
  - Xtals/Crystals
- Home Appliance »
- Interface Logic »
- PCIe Packet Switch »
- PCIe/PCI Bridges »
- Power Management »
- ReDriver™ Signal Conditioners »
- Signal Switch/Multiplexers »
- Video Decoder »
- Part Cross Reference »

Sign up for our newsletter

Standard XO Part Quotes

Use this selector to find the standard XO solution to fit your needs. Select by any of the parameters below to help narrow your search. This selector also provides price quotes for quantities under 1000 units.

This is not a complete list of all our crystal oscillator solutions. More solutions can be found on our ASSP XO, HiFlex™ XOs, VCXO, SSXO, Standard XO or Xtals pages.

Not finding the solution you need? Try building a custom HiFlex XO Part, or requesting a custom quote.

FIND STANDARD XO PART QUOTES | FAQ

Find Standard XO Part Quotes

Select the parameters below to find the solution you need. Show All

Family	Freq. (MHz)	Output Logic	Package Size	Supply Voltage	Stability (ppm)*	Temperature
FK 3.3V	1–9.999 (7)	CMOS (44)	3.2x2.5 (44)	3.3 (44)	25 (6)	**-40/+85C**
[Show All]	10–19.999 (9)				50 (38)	**[Show All]**
	20–29.999 (9)					
	30–39.999 (4)					
	40–49.999 (1)					
	50–59.999 (2)					

1–44 of 44 Results

Part Number	Product Family	Frequency (MHz)	Output Logic	Package Size	Stability (PPM)	Supply Voltage	Temp. Range	Photo	Request Quote
FK0180006	FK 3.3V	1.843	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK0360004	FK 3.3V	3.686	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK0400007	FK 3.3V	4.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK0500002	FK 3.3V	5.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK0530001	FK 3.3V	5.330	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK0800004	FK 3.3V	8.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK0810003	FK 3.3V	8.192	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK1000008	FK 3.3V	10.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK1200011	FK 3.3V	12.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK1220009	FK 3.3V	12.288	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK1300011	FK 3.3V	13.000	CMOS	3.2x2.5	25	3.3	-40/+85C		Get Quote
FK1430003	FK 3.3V	14.318	CMOS	3.2x2.5	25	3.3	-40/+85C		Get Quote
FK1600005	FK 3.3V	16.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK1630005	FK 3.3V	16.384	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK1840003	FK 3.3V	18.432	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK1940004	FK 3.3V	19.440	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK2000025	FK 3.3V	20.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK2000026	FK 3.3V	20.000	CMOS	3.2x2.5	25	3.3	-40/+85C		Get Quote
FK2400014	FK 3.3V	24.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK2400017	FK 3.3V	24.000	CMOS	3.2x2.5	25	3.3	-40/+85C		Get Quote
FK2450010	FK 3.3V	24.576	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK2500022	FK 3.3V	25.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK2500025	FK 3.3V	25.000	CMOS	3.2x2.5	25	3.3	-40/+85C		Get Quote
FK2600019	FK 3.3V	26.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK2700018	FK 3.3V	27.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK3000006	FK 3.3V	30.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK3300008	FK 3.3V	33.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK3530003	FK 3.3V	35.328	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK3680003	FK 3.3V	36.864	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK4800011	FK 3.3V	48.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK5000013	FK 3.3V	50.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK5400007	FK 3.3V	54.000	CMOS	3.2x2.5	25	3.3	-40/+85C		Get Quote
FK6250005	FK 3.3V	62.500	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK6400003	FK 3.3V	64.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK6600006	FK 3.3V	66.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK6660007	FK 3.3V	66.667	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK6660009	FK 3.3V	66.670	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK7420004	FK 3.3V	74.250	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK7500009	FK 3.3V	75.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FK7770003	FK 3.3V	77.760	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FKA000006	FK 3.3V	100.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FKA620006	FK 3.3V	106.250	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FKC500001	FK 3.3V	125.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote
FKD300002	FK 3.3V	133.000	CMOS	3.2x2.5	50	3.3	-40/+85C		Get Quote

1–44 of 44 Results

Copyright © 2012 Pericom Semiconductor Corporation

Downloaded from Arrow.com.