TXR41AB90-1410AI2 Product Details



TXR41AB90-1410AI2

TE Internal Number: 372139-000

Active

Braid, Fixed, Spin and Tinel Lock Adapters

Not EU RoHS or ELV Compliant

Product Highlights:

- Terminate To Cable
- Style = Tinel Lock Braided
- Connector Code = 41
- 90°
- Shell Size = 14, 15

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information

Product Drawings:
- Tinel-Lock Adapter (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Style = Tinel Lock Braided
- Shell Size = 14, 15
- Material = Aluminum Alloy
- Finish = Cadmium Plating over Electroless Nickel
- Color = Olive Drab

Electrical Characteristics:
- Angle = 90°
- Entry Size = 10
- Boot Diameter (mm [in]) = 23.49 [0.925]
- Entry Diameter (mm [in]) = 15.87 [0.625]
- Finish Code = B

Body Related Features:
- Connector Code = 41
- Cable Diameter (Max.) (mm [in]) = 15.37 [0.605]

Configuration Related Features:
- Braid = Preattached Single 36 AWG Braid
- Material Code = A

Industry Standards:
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:
- Terminate To = Cable

Other:
- Brand = Raychem

BOOKMARK

© 2009 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com.