

3M United States > All 3M Products > Protective Eyewear > Safety Glasses > 3M™ Privo™ Protective Safety Glasses >

3M™ Privo™ Protective Eyewear 12261-00000-20, Clear Anti-Fog Lens, Black Frame, 20 EA/Case

3M ID 70071541265, UPC 10078371620872



Overview

Specifications

Details

Resources

Product Support



[View Images and Video](#)

- European-inspired styling adds a look of sophistication
- Fashion appearance allows use on and off the jobsite
- Lenses slightly wrap for additional coverage
- Soft nose bridge and temple tips offer all-day comfort

[View all details](#)

WHERE TO BUY

Select One



Select One



Specifications

Attribute Name	Value
Brand	Privo™
Case Quantity	20
Class	Value
Comfort Features	Soft nose bridge, temples, and tips
Eyewear Range	Value
Frame Color	Black
Frame Material	Plastic
Frame Style/Type	Half-frame
Lens Coating	Anti-Fog
Lens Color	Clear
Lens Marking	Z87+U6
Lens Material	Polycarbonate

National Stock Number 4240015915182

Product Type Safety Glasses

Recommended Industry Automotive , Construction , Food and Beverage Manufacturing , General Manufacturing , Metal Fabrication , Military Maintenance, Repair and Operation (MRO) , Military Tactical , Mining , Oil & Gas , Pharmaceuticals , Transportation

Size One size fits most

Splash Protection No

Standards/Approvals ANSI Z87.1-2003 , CSA Z94.3-2007

Temple Color Black/Orange

Temple Style Soft temple tips

UV Protection 99.9%

Details

- European-inspired styling adds a look of sophistication
- Fashion appearance allows use on and off the jobsite
- Lenses slightly wrap for additional coverage
- Soft nose bridge and temple tips offer all-day comfort
- Polycarbonate lenses absorb 99.9% UV

Stylish Privo unisex protective eyewear looks as smooth as it functions. Bridges eurostyle and comfort with soft tips and temples, a gentle nose bridge, and a sturdy polycarbonate lens. Anti-fog coating allows for all-day, indoor or outdoor use.

3M™ Privo™ Protective Eyewear combines a sophisticated European style with the practicality of safety glasses. The glasses provide the eye safety needed on the job, with a sleek appearance that looks fashionable away from the jobsite. Combining function with fashion, the slight wrap of the lenses looks stylish and offers extra eye protection. To make the glasses comfortable for all-day wear, they have been fitted with a soft nose bridge and temple tips that cushion high contact points. The impact-resistant polycarbonate lens absorbs 99.9% UV rays. These safety glasses are recommended for the following tasks: assembly and mechanical, chipping, chiseling, drilling, grinding, machining, masonry, metal repair, painting, pouring/casting, power fastening, riveting, sanding and sawing. Industries in which these safety glasses are commonly used include aviation, construction, food and beverage, general manufacturing, mining, oil and gas, primary metals and transportation. Privo™ safety glasses meet the requirements of CSA Z94.3-2007 and the high impact requirements of ANSI Z87.1-2003.

Eye protection is important to safeguard your eyes and maintain healthy vision. According to the Bureau of Labor Statistics, nearly three out of every five workers who suffered eye injuries were not wearing eye protection at the time of the accident. Wearing the correct safety eyewear for the task and for the unique needs of the worker is important. 3M™ recognizes the need to design comfortable and attractive eyewear, increasing the usage of safety glasses on the job. That's why all 3M™ protective eyewear combines safety features with comfort enhancements.

Suggested Applications

- Clear lens.
- Black frame with orange accent temple tips.
- Polycarbonate lens absorbs 99.9% UV.
- Meets the requirements of CSA Z94.3-2007 and the High Impact Requirements of ANSI Z87.1-2003.
- 20 safety glasses per case.

Resources

Brochure

[Protective Eyewear Line Card \(PDF, 701.7KB\)](#)

[3M™ Total Eyewear Solutions Trifold Brochure \(PDF, 2.0MB\)](#)

Product Support

Specific product and application questions

**SEND US A
MESSAGE**

**Product
Support
1-800-
243-4630**

**Sales
Support
1-800-
328-1667**

3M United States

PRODUCTS

[Abrasives](#)
[Adhesives & Tapes](#)
[Chemicals & Advanced
Materials](#)
[Films](#)
[Filtration](#)
[View All Products](#)

INDUSTRIES

[Automotive](#)
[Commercial Solutions](#)
[Communications](#)
[Consumer](#)
[Design & Construction](#)
[Electronics](#)
[Energy](#)
[Health Care](#)
[Manufacturing](#)
[Mining, Oil & Gas](#)
[Safety](#)
[Transportation](#)

BRANDS

[Post-it](#)
[Scotch](#)
[Scotch-Brite](#)
[Command](#)
[Filtrete](#)
[Nexcare](#)
[ScotchBlue](#)

HELP

[Help Center](#)

REGULATORY

[SDS Search](#)
[Transport Information
Search](#)
[RoHS & REACH
Information Search](#)
[CPSIA Certification
Search](#)
[California Supply
Chains Act Disclosure
\(PDF, 84KB\)](#)
[UK Modern Slavery
Act Statement \(PDF,
169KB\)](#)
[More Regulatory &
Compliance
Information](#)

NEWS

[Particles by 3M](#)
[Press Releases](#)

ABOUT US

[About 3M](#)
[3M Careers](#)
[Investor Relations](#)
[Partners & Suppliers](#)
[Government
Customers](#)
[Sustainability](#)
[3Mgives](#)

SEARCH 3M



FOLLOW US



United States [English](#)



[Legal](#) | [Privacy](#)
© 3M 2018. All Rights Reserved.

The brands listed above are trademarks of 3M.