
Part Number : 2037026300
Product Description : FineAdjust Applicator for Mini-Fit Crimp Terminals, Double 22+22 AWG
Series Number : 207127
Status : Active
Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

2037026300-000.pdf

TM-638000029-001.pdf

TM-638004900-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Mini-Fit Crimp Terminals, Double 22+22 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust,Mini-Fit,Mini-Fit Jr.,Mini-Fit Plus
Tool Type	Applicator
UPC	193264415588
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where

Downloaded from Arrow.com.

	Molex Tooling is modified.

Physical

Net Weight	1.000/g

Applicable Parts

Description	Part Number
Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, Double 22+22 or Single 24-18 AWG, Reel	39000038
Mini-Fit Male Crimp Terminal, Matte Tin (Sn) Plated Brass, Double 22+22 or Single 24-18 AWG, Reel	39000040
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, Double 22+22 or Single 24-18 AWG, Reel	39000059
Mini-Fit Male Crimp Terminal, Matte Tin (Sn) Plated Phosphor Bronze, Double 22+22 or Single 24-18 AWG, Reel	39000061
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 24-18 AWG, Reel	39000073
Mini-Fit Male Crimp Terminal, 0.38µm Selective Gold (Au) Plated Brass, Lead-Free, 24-18 AWG, Reel	39000075
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass, 24-18 AWG, Reel	39000120
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Brass, 24-18 AWG, Bag	39000121
Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Phosphor Bronze, 24-18 AWG, Reel	39000126

Downloaded from Arrow.com.

Mini-Fit Female Crimp Terminal, Selective Gold (Au) over Phosphor Bronze, 24-18 AWG, Reel	39000181
Mini-Fit Female Crimp Terminal, Tin (Sn) over Nickel (Ni), 24-18 AWG, Reel	39000207
Mini-Fit Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 24-18 AWG, Reel	39000213
Mini-Fit Male Crimp Terminal, 0.76µm Selective Gold (Au) Plated Phosphor Bronze, 24-18 AWG, Reel	39000219
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 24-18 AWG, Reel	39000428
Mini-Fit Male Crimp Terminal, 0.76µm Selective Gold (Au) Plated Brass, Lead-Free, 24-18 AWG, Reel	39000430
Mini-Fit Female Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 24-18 AWG, Reel	40130851

Downloaded from Arrow.com.