



RW-200-E-7/8-0-SP Product Details

[Share](#) [Print](#) [Email](#)


✔ Active

Heat Shrink Tubing

RW-200-E-7/8-0-SP

RW-200-E-7/8-0-SP

TE Internal Number: CB83464003

Product Highlights [View All](#)

- Heat Shrinkable Tubing
- Product Name = DR-25, RW-200
- Product Source = U.K.
- Flexible
- Medium Wall Style

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Type [?]	Heat Shrinkable Tubing
Color	Black

Dimensions

Expanded ID, Min. (mm [in]) [?]	21.50 [0.847], 21.70 [0.854], 21.90 [0.861], 22.10 [0.870], 22.20 [0.875]
Recovered ID, Max. (mm [in]) [?]	11.10 [0.437], 11.20 [0.440], 11.265 [0.443], 11.363 [0.447], 11.40 [0.450]
Cut Length (mm [in]) [?]	48.00 [1.890]

Body Features

Product Name [?]	DR-25, RW-200
Pliancy	Flexible
Wall Style [?]	Medium
Wall Type [?]	Dual, Single
Lining Type [?]	Adhesive
Material	Crosslinked Elastomer, Crosslinked Fluoroelastomer
Shrink Ratio [?]	2:1
Fluid Type	Aviation Fuel, Diesel Fuel, Hydraulic Fluid, Lubricating Oil
Resistant To	Abrasion, Fluids, Mechanical Damage
Wall Thickness - Full Recovery (Nominal) (mm [in])	1.50 [0.059]

Housing Features

Material Systems	Yes
Material Systems Code [?]	25, 200

Industry Standards

Government/Industry Qualification	No
Flammability Rating	Flame-Retardant
UL Rating	None
CSA Certified	No
Approved Standards	DEF Std 59-97 Issue 3 Type 6B, RT-3037, SAE AMS-DTL-23053/17, VDE 0341 Part 9005 Type A, VG95343 Part 5D Type D
RoHS/ELV Compliance [?]	RoHS compliant, ELV compliant
Lead Free Solder Processes [?]	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental

Fluid Resistance	Splash Protection
Operating Temperature (°C) [?]	-40 - +200, 225

Conditions for Usage

Full Recovery Temperature (°C)	175
Shrink Temperature, Min. (°C)	100, 150
High Temperature Compatible	Yes

Operation/Application

Emission Free	No
Product Use	Cables, Electronic Components, Harnesses
Application	Aerospace, Harness Protection, Insulation and Protection, Military

Packaging Features

Packaging Method	Spool
------------------	-------

Product Availability

Product Source	U.K.
----------------	------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

