

**ML-50-S1BXF****ML-50-S1BYF****ML-50-S1BXS****ML-50-S1BYS**

Enlarge : Click picture, drawing.

| [Back](#) | [List](#) | [Next](#) |

To be Followed by part number.

Specification	ML-50-S1BXF/S	ML-50-S1BYF/S
Rating	250V-15A	
With standing V	AC2000V(1minute)	
Insulation Ω	DC500V,1000M Ω Min	
Safety approvals	UL	
Number of poles	1 up to 20	1 up to 22
Insulation materials		
Pitch	10.16mm	
Screw	F:Screw with square washer (M4X8),S:Screw with washer (M4X8)	
Terminal style	PCB	
Body color	Black	
Optional accessories	Cover:ML-50-4C	-
	Name plate:ML-50-4K	-
	Name plate metal holder:ML-50-4I1 (Need 2 pcs for 1terminal block)	-
	Mounting screw:ML-40-3J (Need 2 pcs for 1terminal block)	-
	Terminal block angled metal holder:ML-50-4L1(Need 2 pcs for 1terminal block)	
	Soldering metal:ML-50-4G1	
	Short circuit metal:ML-1000-4H1,4H2,4H5,4H6,4H9	
	Banana plug adapter : TJ-3-B-4	
	Terminal block banana plug:TJ-3-A	
Important notice	Except 20 Poles remaining scratch marks at the end due to cutting by pole	





How To Order

ML - 50 - S1BX  		
Series	Type	Number of poles
ML - 50	F : Screw with square washer (M4 X 8)	1 up to 20
	S : Screw with washer(M4 X8)	

ML - 50 - S1BY  		
Series	Type	Number of poles
ML - 50	F : Screw with square washer (M4 X 8)	1 up to 22
	S : Screw with washer(M4 X8)	

ML-50-S1BXF

ML-50-S1BYF

**ML-50-S1BXS****ML-50-S1BYS**

UP DATE: 6/30/2006

[Back](#)[Home](#)

- The contents of these document are subject to change without previous notice for improvements in product performance.
- When using the products, please confirm with the specifications which will be provided to you upon request. Individual specifications prior to the catalog specification.
- The appearance of product's color may differ from original upon your monitor or operating system.
- The latest information to receive please consult our marketing either phone call or e-mail.

e-mail: marketing@satoparts.co.jp
[| Company profile](#) | [| Site map](#) | [| Ask](#) | [| Notice and hint](#) | [| Renewal record](#) | [| Japn Web site](#) |

Copyright (C) 2001-2006 SATO PARTS CO., LTD. All Right Reserved.