



Twist Locks, Standard

Features

- Fast, Economical Way to Securely Position and Hold Wire, Cable, or Tubing
- A Single Twist Locks or Unlocks the Bundle for Ease of Use
- Tough, Resilient, Natural Nylon 6/6 Molded Construction



TL-01




Standard Twist Locks

	NTE Type No.	Description	H Ref.	Bundle Dia.		Qty. per Bag	Diag No.
				Min	Max		
NEW	04-TL19	3/8" Lock	1.080 / 27.4	.300 / 7.62	.400 / 10.2	25	TL-01
NEW	04-TL29	1/2" Lock	1.200 / 30.5	.400 / 10.2	.500 / 12.7	25	TL-01
NEW	04-TL39	5/8" Lock	1.260 / 32.0	.550 / 13.9	.650 / 16.5	25	TL-01
NEW	04-TL49	3/4" Lock	1.550 / 39.4	.700 / 17.8	.800 / 20.3	25	TL-01
NEW	04-TL59	1 1/8" Lock	2.170 / 55.1	1.200 / 30.5	1.300 / 33.0	25	TL-01
NEW	04-TL69	1 3/8" Lock	2.670 / 67.8	1.450 / 36.8	1.550 / 39.4	25	TL-01
NEW	04-TL79	1 1/2" Lock	2.930 / 74.4	1.550 / 39.4	1.650 / 41.9	25	TL-01


Twist Locks, Supports w/Adhesive

Features

- Twist Lock Supports on an Adhesive Base
- Fast, Economical Way to Securely Position and Hold Wire, Cable, or Tubing
- A Single Twist Locks or Unlocks the Bundle for Ease of Use
- Tough, Resilient, Natural Nylon 6/6 Molded Construction



TL-02




Twist Lock Supports on Adhesive Base

	NTE Type No.	Description	A Ref.	B	D	E	Max Bundle Dia.	Qty. per Bag	Diag No.
NEW	04-TLS19	.450 Lock	1.070 / 27.18	2.149 / 54.58	1.000 / 25.4	1.000 / 25.4	.450 / 11.43	10	TL-02
NEW	04-TLS29	.450 Lock	.190 / 4.83	1.230 / 31.24	1.000 / 25.4	.520 / 13.21	.450 / 11.43	10	TL-02
NEW	04-TLS39	.580 Lock	.190 / 4.83	1.400 / 35.56	.870 / 22.1	.520 / 13.21	.580 / 14.73	10	TL-02


Twist Locks, Label

Features

- Integral Label Area for Writing
- Permanent Ink Pens, Felt Tip Pens, Pressure-Sensitive Adhesive Label, or Post-it® Notes can be used
- Fast, Economical Way to Securely Position and Hold Wire, Cable, or Tubing
- A Single Twist Locks or Unlocks the Bundle for Ease of Use
- Tough, Resilient, Natural Nylon 6/6 Molded Construction



TL-03



Twist Locks with Label

	NTE Type No.	Description	L	Max. Bundle Dia.	Qty. per Bag	Diag No.
NEW	04-LTL19	1/4" Lock	3.094 / 78.59	.250 / 6.35	25	TL-03
NEW	04-LTL29	3/8" Lock	3.281 / 83.34	.375 / 9.53	25	TL-03