Datasheet for part number DCSFY-37S

Our Catalog Part Number: DCSFY-37S
Our Global Manufacturing Part Number: 115153-0115 Y
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*SF

Product Datasheet	
General	Speedy D connector terminate ribbon cables without stripping and without splicing
Wire Gauge Range AWG	AWG 26-28
Mating Cycles	50
Dielectric Withstanding Voltage	780 VAC at sea level
Current Rating	1.5 A max
Contact Resistance	15 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	37 contacts size 20
Gender	Socket
Contact Type	stamped
Contact Material	copper alloy
Contact Finish	gold flash (Performance Class 3)
Contact Termination	IDC
Mounting Methode	Dual Float Mount
Accessory	supplied without strain relief

Specifications and dimensions subject to change.

Downloaded from Arrow.com.