
TRACO POWER


Common Mode Choke

TCK-086


Order Code	TCK-086
Inductance (each winding)	156 µH ±35% (at 100 kHz / 100 mV)
Impedance (DCR)	2.5 mΩ max.
Rated Current	25 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-086



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	16.6 ±0.4
B	16.4 ±0.4
C	12.5 max.
D	5.0 ±1.0
E	14.1 ±0.5
F	6.1 ±0.5
G	ø 1.8 max.

All specifications valid at +25°C, unless otherwise stated.

© Copyright 2026 Traco Electronic AG Specifications can be changed without notice.

Downloaded from Arrow.com.