© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	REV PER ECR-22-149214	18AUG2022	LP	DSC



AMP WIRE RANGE
2/0 AWG SOLID OR STRANDED

1 STAMP "AMP 2/0W* ", LOCATED APPROX AS SHOWN

2 NOTE DELETED

3 NOTE DELETED

4 MATERIAL:
COPPER PER ASTM B152, ANNEALED

5 FINISH:
NICKEL PLATE 0.00762[.000300] MIN EXT THK PER SAE AMS-QQ-N-290

6 MATERIAL THK: 2.007±0.076[.079±.003]

QTY	PACKAGE TYPE	PART NO.
25	LOOSE PIECE	132104-2

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 343°C [650°F]

VOLTAGE RATING: N/A

WIRE CROSS SECTIONAL AREA RANGE: 60.6-76.3mm²[119,500-150,000] SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± –
2 PLC	± –
3 PLC	± 0.127[.005]
4 PLC	± –
ANGLES	± –

MATERIAL 4

FINISH 5

DWN	JR RUTH	25JAN10
CHK	T MICHIELUTTI	25JAN10
APVD	T MICHIELUTTI	25JAN10
PRODUCT SPEC	—	
APPLICATION SPEC	114-2162	
WEIGHT	—	

TE Connectivity

NAME: TERMINAL, RING TONGUE, STRATO-THERM, HR, SOLISTRAND, WIRE SIZE: 2/0 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-132104	—

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV B3

Downloaded from Arrow.com.