


TUNING KNOBS 'CLASSIC'

Practical Range of Tuning Knobs

Choose a knob that meets your own special size and design requirements. OKW TUNING KNOBS are suitable for many different applications and are offered in thermoplastic for normal use and thermosetting plastic (Duroplast) for high temperature resistance requirements.

- different designs and sizes: practical, with a good grip
- high-grade metal effect with aluminum cap or insert embellisher; the color and styling of your front panel thus forms a unified whole
- models with markings; advantageous for adjusting and indicating
- lateral screw fixing for rotary potentiometer with shaft ends
- sizes from $\varnothing$ 12 to $\varnothing$ 38 mm with spindle sizes 4 mm or 6 mm
- accessory insert: reduces borehole from 6 to 4 mm



View Customizing Options

What do you still need for your own very personal product? We can supply enclosures and tuning knobs with all necessary modifications for fitting your electronic components. Customizing options for Tuning Knobs 'classic'


TUNING KNOBS 'CLASSIC'



Machining



Printing



Installation / Assembly
of accessories

Select Versions



A1310560
TUNING KNOB, with lateral
screw fixing
PC
black RAL 9005
15.4x13.2mm 6mm



A1311860
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
18.8x12.5mm 6mm



A1312560
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black RAL 9005
20.7x19.7mm 6mm



A1313540
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
20x15.4mm 4mm



A1313560
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
20x15.4mm 6mm



A1314240
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black/alu
14.1x14mm 4mm



A1316240
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black RAL 9005
16.4x12.3mm 4mm



A1317860
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
20.3x12.8mm 6mm



A1318260
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black/alu
18.2x14.2mm 6mm



A1318560
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black/alu
23.9x16mm 6mm



A1319260
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
18.9x13.5mm 6mm



A1319560
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
29x20.1mm 6mm

TUNING KNOBS 'CLASSIC'



A1319860
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
20.3x18mm 6mm



A1320260
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black/alu
20x16mm 6mm



A1321060
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
31x20mm 6mm



A1321160
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black RAL 9005
20x16mm 6mm




A1321260
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black/alu
21x10mm 6mm



A1321860
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
23x16mm 6mm



A1324260
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black/alu
24.3x16mm 6mm



A1324860
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black RAL 9005
25x20mm 6mm



A1328160
TUNING KNOB, with lateral
screw fixing
PF (UL 94 V-0)
black/alu
28x16mm 6mm



A1412441
TUNING KNOB, with lateral
screw fixing
PC
brilliant
12x7.2mm 4mm



A1412461
TUNING KNOB, with lateral
screw fixing
PC
brilliant
12x7.1mm 6mm



A1416449
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
15.9x15mm 4mm



A1416469
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
15.9x15.2mm 6mm



A1418260
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black/alu
18.6x12mm 6mm



A1418261
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
18.7x12mm 6mm



A1418461
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
17.8x12mm 6mm

TUNING KNOBS 'CLASSIC'



A1421469
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
22.1x14.3mm 6mm



A1422260
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black/alu
22.8x13mm 6mm



A1422261
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
23x13mm 6mm



A1422461
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
22.5x13.3mm 6mm



A1422469
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
22.2x17.9mm 6mm



A1432260
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black/alu
33x14.3mm 6mm



A1432261
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
32.8x14.4mm 6mm



A1432469
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
31.9x14mm 6mm



A1438261
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
38.9x16mm 6mm



A1438461
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
brilliant
37.8x15.9mm 6mm



A1613560
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black RAL 9005
19.9x15.5mm 6mm



A1624260
TUNING KNOB, with lateral
screw fixing
ABS (UL 94 HB)
black/alu
24x12.4mm 6mm



A1685540
TUNING KNOB, with lateral
screw fixing
PC
black RAL 9005
11.4x10.5mm 4mm

TUNING KNOBS 'CLASSIC'

Accessory



A1300040

Insert

ABS (UL 94 HB)

black RAL 9005

7.4x7mm 4mm

Subject to technical modification without notice. © by OKW Gehäusesysteme, Buchen/Germany.