

D2.5/8.N.ADO.EX



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

General Information

Extended Product Type:	D2.5/8.N.ADO.EX
Product ID:	1SNA146039R2400
EAN:	3472591460391
Catalog Description:	D2.5/8.N.ADO.Ex IDC Terminal Blocks
Long Description:	D2.5/8.N.ADO.Ex IDC Terminal Blocks - Feed-through - Blue,2.5mm ² Rated CrossSection, 8mm Spacing TH 35-7.5, TH 35-15 Rail.

Ordering

Color:	blue
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160004C0204
Instructions and Manuals:	1SNC160004C0204

Dimensions

Product Net Width:	8 mm
Product Net Height:	45 mm
Product Net Depth / Length:	41 mm
Product Net Weight:	9 g

Technical

Rated Cross-Section:	2.5 mm ²
Spacing:	8 mm
Connection Type:	ADO System
Function:	Feed-through
Number of Levels:	1
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	------------------------------------------------------

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	-----------------------------------------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225054U1001
EAC Certificate:	1SND161010A1100
Environmental Information:	1SND220024E1003
Instructions and Manuals:	1SNC160004C0204
RoHS Information:	1SND230472F0201

Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	81 mm
Package Level 1 Depth / Length:	220 mm
Package Level 1 Height:	47 mm
Package Level 1 Gross Weight:	0.45 kg
Package Level 1 EAN:	3472591460391
Package Level 2 Units:	750 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 2 Gross Weight:	6.75 kg
Package Level 3 Units:	36000 piece
Product Packing Type:	Box



