Part Number : 133580681
Product Description : RFID Tag, 25.9m Read Range on Metal, 19.8m Read Range Off Metal, For Multiple Surfaces Including Metal and Non-Metal, 144.80 by 37.60mm Footprint, Screw or Rivet Attachment
Series Number : 13358
Status : Obsolete
Product Category : Asset Tracking



Documents and Resources

Drawings

133580681_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Asset Tracking
Series	13358
Description	RFID Tag, 25.9m Read Range on Metal, 19.8m Read Range Off Metal, For Multiple Surfaces Including Metal and Non-Metal, 144.80 by 37.60mm Footprint, Screw or Rivet Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Metal or Non-Metal Surfaces
UPC	193264037155

Electrical

Frequency	902-928 MHz

Physical

Dimensions	144.80 x 37.60 x 6.90mm
Length	144.80mm
Mounting Style	Adhesive, Screws
Packaging Type	Bag
Read Range	19.8m Off Metal, 25.9m on Metal
Thickness	6.90mm
Width	37.60mm

Obsolete

Downloaded from Arrow.com.