
Part Number : 1731120084
Product Description : FCT High Power Contact, Female, Straight, PCB Through Hole, 0.80µm Gold Mating Plating, 5.00µm Tin Termination Plating, Split Tine, 20.0A, 3.15mm PCB Drilling Diameter
Series Number : 173112
Status : Active
Product Category : D-Sub Contacts
Engineering Part Number : FMP010S104



Documents and Resources

Drawings

1731120084_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

1731120008-PK-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:376c6fe0-f0bd-46c2-bec2-1443d46317fd
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT High Power Contact, Female, Straight, PCB Through Hole, 0.80µm Gold Mating Plating, 5.00µm Tin Termination Plating, Split Tine, 20.0A, 3.15mm PCB Drilling Diameter
Contact Type	High Power
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056324359

Electrical

Current - Maximum per Contact	20.0A

Physical

Durability (mating cycles min)	500
Gender	Female
Material - Contact	Copper Alloy

Downloaded from Arrow.com.

Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	1.500/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	0.800µm
Plating min - Termination	5.000µm
Temperature Range - Operating	-55° to +155°C
Termination Style	Through Hole

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

Application Tooling

Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	1731121747

Downloaded from Arrow.com.