Part Number : 511910700
Product Description : 2.50mm Pitch Mini-Latch Wire-to-Wire and Wire-to-Board Receptacle Housing, with Guide Rails, 7 Circuits
Status : Not Recommended For New Design
Product Category : Connector Housings



Documents and Resources

Drawings

511910700_sd.pdf

511910700_stp.zip

Specifications

511910000-AS-000.pdf

511919200-SPK-200.pdf

2055050000-PS-000.pdf

511910000-PS-000.pdf

PS-51191-003-001.pdf

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	51191
Description	2.50mm Pitch Mini-Latch Wire-to-Wire and Wire-to-Board Receptacle Housing, with Guide Rails, 7 Circuits
Application	Wire-to-Board, Wire-to-Wire
Component Type	Receptacle
Product Name	Mini-Latch
UPC	800753327818

Agency

Downloaded from Arrow.com.

UL	E29179

Physical

Circuits (maximum)	7
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	704.700/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description
Mini-Latch / KK Single Row Vertical Headers
Mini-Latch / KK Single Row Right-Angle Headers
Mini-Latch Single Row Plug Housings

Use with Part(s)

Description
Mini-Latch Female Crimp Terminals

Downloaded from Arrow.com.