


KIT PART NUMBER	CONNECTOR PART NUMBER	KIT TYPE	PCB CONTACT PART NUMBER	CONTACTS QTY.	MS REF NUMBER	CAP/CONTAINER PROTECTION
10-565997-753N	88-565759-35S				D38999/24WJ35BN	
10-565997-753A	88-565759-35H				D38999/24WJ35BA	
10-565997-753B	88-565759-35J				D38999/24WJ35BB	10-576238-002
10-565997-753C	88-565759-35L				D38999/24WJ35BC	10-576237-002
10-565997-753D	88-565759-35N				D38999/24WJ35BD	
10-565997-753E	88-565759-35T				D38999/24WJ35BE	

ALTERNATE SHELL ROTATION
CONNECTOR LESS STAMPING SEE NOTE 4
FOR REQUIRED STAMPING



SCALE 2

5. AFTER CONTACTS HAVE BEEN INSTALLED, PLACE CONNECTOR INTO CONTAINER AND CAP. TO INSURE CAP LOCATION, APPLY TAPE IF NEEDED. CARE MUST BE TAKEN NOT TO BEND THE CONTACTS.

4. STAMP "AMPHENOL", PART NUMBER, DATE CODE (9-3895), AND LOT NUMBER PER 9-5788
EXAMPLE:

AMPHENOL 10-565997-753B 0844 001000

3. PROCESS SPEC.:
SPECIAL CONTROL 9-6000-2
PROCESS SHEET CONTROL 9-4796
9-3895, 9-5788

2. PACKAGE PER PRODUCTION PROCESS SHEET

1. KIT TYPE I CONTACTS ARE SHIPPED UNASSEMBLED.
KIT TYPE II CONTACTS ARE SHIPPED ASSEMBLED IN CONNECTOR.

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED.
HOWEVER, DOCUMENTS REFERENCED HEREON
MAY CONTAIN LIMITED RIGHTS DATA.

N/A		PRO/ENGINEER INFORMATION
N/A		Pro/e Model Used: 10-565997-750.ASSEM
NEXT ASSEMBLY		Drawing Name: 10-565997-753



RELEASED / Nov. 05 2008, 08:40 AM

10-565997-753

SHEET 1 OF 1

REV. A

FOR UNIT ILLUSTRATION AND DIMENSIONAL DATA
SEE 10-536197-DS TYPE 1



SECTION A-A

R-435
RELIABILITY
CONTROL

3	I	SEE COLUMN	CAP/CONTAINER	5
2		SEE COLUMN	CONTACT	
1	I	SEE COLUMN	CONNECTOR	
SPECIFICATIONS				
POS	QTY	PART NUMBER	DESCRIPTION	NOTE
PARTS LIST				
AMPHENOL CORPORATION 40-60 DELAWARE AVENUE SIDNEY, NY. 14838				
KIT, CONNECTOR TYPE MS AB-STAMPING, TV D38999/24WJ35B()				
SIZE	CAGE CODE	DOCUMENT NO.		REV.
C	77820	10-565997-753		A
SCALE: 1.0	REF: 88-565750/759	SHEET 1 OF 1		