


[My Cart](#)[My Part Lists](#)[Sign In/Register](#)[English \(Change\)](#)

Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [Support Center](#) [My Account](#)**1057780-1 Product Details**[Share](#)[Print](#)[Email](#)**1057780-1**

(3152-1201-10)

TE Internal Number: 1057780-1

[Active](#)**TNC RF Connectors**[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)**Product Highlights:**

- Connector - RF
- Jack
- Applies To Wire/Cable
- Coaxial Cable Termination Type = Solder
- Body Style = Straight

[View all Features](#)**Quick Links**

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)**Documentation & Additional Information****Product Drawings:**

- [OST 4 HOLE FLANGE MOUNT JACK RECEPTACLE STRAIGHT TER...](#) (PDF, English)

Catalog Pages / Data Sheets:

- [TNC Connectors](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)**Related Products:**

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)**Product Type Features:**

- [Product Type](#) = Connector - RF
- [Gender](#) = Jack
- [Body Style](#) = Straight
- [Body Material](#) = Brass
- Weatherproof = No
- [Solder Terminal](#) = Without
- Grade = Commercial
- Dielectric Material = PTFE

Mechanical Attachment:

- [Panel Mount Retention](#) = With
- Panel Mount Retention Type = Flange

Electrical Characteristics:

- [Connector Impedance \(Ω\)](#) = 50

Termination Features:

- [Coaxial Cable Termination Type](#) = Solder

Body Features:

- [Body Plating](#) = Nickel

Contact Features:

- Center Contact Plating = Gold

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Wire/Cable

Other:

- Brand = AMP
- Comment = Captured Center Contact - Straight Terminal

Corporate Information[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)**Quick Links**[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)**Customer Support**[Email or Chat With Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage your Account](#)**Keep Me Informed**

Receive TE News, Events & Technology Updates

Enter your email address

