




55A1161-24-0/2/4/5/6/9-9 Product Details

[Share](#) [Print](#) [Email](#)


✓ Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

55A1161-24-0/2/4/5/6/9-9

55A1161-24-0/2/4/5/6/9-9 

TE Internal Number: 6641593001

Product Highlights [View All](#)


- Cable Type = Spec 55
- Wire Source = United Kingdom, United States
- Cable Style = Round Braid Shielded and Jacketed
- Wire Size (AWG/CM) = 24 AWG
- Voltage Rating = 600 VAC

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Cable Type 	Spec 55
Cable Style	Round Braid Shielded and Jacketed

Electrical Characteristics

Voltage Rating (VAC)	600
----------------------	-----

Body Features

Wire Size (AWG/CM)	24 AWG
Cable Jacket Color	White
Conductor Type	Tin-Coated Copper
Wire Color	Black, Red, Yellow, Green, Blue, White
Nominal Outside Diameter (mm [in])	3.66 [0.144]
Wire Diameter (mm [in])	0.94 [0.037]
Shield Size	38 AWG
Shield Material	Tin Plated Copper

Configuration Features

Number of Conductors	6
----------------------	---

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Temperature Range (°C)	-65 - +150
------------------------	------------

Operation/Application

Application	General Purpose - Light Weight
-------------	--------------------------------

Packaging Features

Wire Source	United Kingdom, United States
-------------	-------------------------------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

