TRACO POWER


Inductor

TCK-151


Order Code	TCK-151
Inductance	4.7 µH ±20% (at 100 kHz / 300 mV)
Impedance (DCR)	150 mΩ max.
Rated Current	1.5 A max.
Operating Temperature	-40°C to +125°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-151



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	3.0 ±0.5
B	3.5 ±0.5
C	2.1 ±0.5
D	1.2 typ.
E	3.6
F	1.7
G	0.8

All specifications valid at +25°C, unless otherwise stated.

© Copyright 2026 Traco Electronic AG Specifications can be changed without notice.

Downloaded from Arrow.com.