

[Cable Assemblies](#) > [Copper Cable Assemblies](#) > [Sensor Cable Assemblies](#)

M12,REAR MOUNTING,MALE,D,2P,0.2M WIRE



✓ ACTIVE

M12 , M12 Connector , M12 PCB/Panel Mount

TE Part # **T4171010502-001**TE Internal #: **T4171010502-001**Connector Type : **Plug**Number of Positions : **2**Keying : **D**Housing Material : **PA66**Cable Assembly Length (mm): **200**

Add to List ▾

[Similar Products](#)

ORDER SAMPLES

[Compatible Parts & Tooling](#)

SHOP OUR DISTRIBUTORS

North America ▾

Request pricing, availability and customization options

CONTACT US



We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

M12,REAR MOUNTING,MALE,D,2P,0.2M WIRE

[M12,REAR MOUNTING,MALE,D,2P,0.2M WIRE](#)

English

CAD Files

3D PDF

[3D_CVM_CVM_T4171010502-001_A.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_T4171010502-001_A.2d_dxf.zip](#) English[ENG_CVM_CVM_T4171010502-001_A.3d_igs.zip](#) English[ENG_CVM_CVM_T4171010502-001_A.3d_stp.zip](#) English

Product Specifications

Product Specification

[ENG_SS_108-106140_A3.pdf](#) EnglishPlease review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



Product Type Features	Assembly Type : Pigtail Connector Type : Plug Shielded : Yes Thread Size : M12 Cable Type : PVC Product Type : Cable Assembly LED : Without
Configuration Features	Number of Positions : 2 Keying : D
Electrical Characteristics	Operating Voltage (VDC): 250 Operating Voltage (VAC): 250
Body Features	Insulation Material : PVC Conductor Material : Copper Alloy Environmental Protection : With Cable Exit Angle : Straight
Contact Features	Contact Current Rating (A): 4
Mechanical Attachment	Mounting Angle : Straight
Housing Features	Housing Material : PA66
Dimensions	Cable Assembly Length (mm): 200 Wire Size (AWG): 22
Usage Conditions	Operating Temperature Range (°C): -40 – 85
Packaging Features	Packaging Quantity : 1 Packaging Method : Bag
Other	Field Serviceable : Yes

Compatible Parts

> [Contact Product Support](#)

Also in the Series | [M12](#)



Circular Connector
Adapters (2)



Circular Connector
Locking & Retention
(1)



Hand Tools (11)



Linear Position
Sensors - LVDT/LVIT
(1)

Also in the Series | [M12 Connector](#)



Sensor Cable
Assemblies (49)



Standard Circular
Connectors (389)

Also in the Series | [M12 PCB/Panel Mount](#)



Sensor Cable
Assemblies (48)



Standard Circular
Connectors (160)

TE News Center

Careers

Investors

Corporate Responsibility

Terms and Conditions of
Sale



What's New on TE.com



Product FAQs

Germany (DE)

China (中文)

Japan (日本語)

Find Your Country/Region ▼

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#)



© 2018 TE Connectivity. All Rights Reserved.