| 插頭部件 (Plug Component) | | | 頭部剝皮尺寸 (Dimensions) | | | 線材規格 (Wire Styls) | 尾部剝皮尺寸 (Dimensions) | | | 端子規格 (Termianl Style ) | |
|---|---|---|---|---|---|---|---|---|---|---|---|
| 顏色(Color) | 零件描述(Component) | Qty. | 內剝(Strip) | 外剝(ROJ) | 顏色(Color) | SJT 16AWGx3C<br>105°C 黑色 (Black)<br>Length : 1500±50 (59.1"±2") | 外剝(ROJ) | 內剝(Strip) | 顏色(Color) | 規格描述(Instruction) | 端子編號(Style No.) |
| 35P 黑色 (Black) | FM-302L (IEC 60320, C13) | 1 | $6^{+1}_{-0}$ | 18 ± 2 | 黑/Black(L) | | 50.8±5 | 6.35±3 | 黑/Black(L) | 絕緣依尺寸剝除,留膠於線上 (Strip and Retain Outside Insulated) | |
| 銅本色 (Brass-Natural) | 2.0*4.0 方管端子(GEM 98752A-0) (2.0*4.0 Receptacle Terminal) | 3 | $6^{+1}_{-0}$ | 18 ± 2 | 白/White(N) | | 50.8±5 | 6.35±3 | 白/White(N) | 絕緣依尺寸剝除,留膠於線上 (Strip and Retain Outside Insulated) | |
| 米白色 (Off-White) | GA005-5 品字母插兩件式內模 (Computer 2x4 Serial Housing) | 1 | $6^{+1}_{-0}$ | 18 ± 2 | 綠/Green(E) | | 50.8±5 | 6.35±3 | 綠/Green(E) | 絕緣依尺寸剝除,留膠於線上 (Strip and Retain Outside Insulated) | |







FM-302L (IEC 60320, C13, RA)
(Dimensions of Connector Face)




SJT 16AWGx3C截面圖
(Wire Cross-Section)




B-C1 扎線圖示 (Tied Loop Hank Detail)

| REV | DATE | REVISE CONTENT |
|---|---|---|
| A | 08/29-2012 | The first edition is issued and drawing. |
| | | |
| | | |
| | | |
| | | |

NOTE :
1 、Hi-Pot Test : 1500V/1Sec ; <0.5mA.
2 、Insulation Resistance Test : DC 500/min>100 meg-ohm.
3 、Continuity & Polarization Test : No short circuit, break circuit, displacement.
4 、Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening.
5 、Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening.
6 、All material according to Non-toxic standard.(Material must be RoHS compliant.)
7 、"FMC" logo maybe present on C13.

| | | | |
|---|---|---|---|
| 線材印字 (Wire Printed) | 充實, 油墨印字 (Un-Fillers, Printing Ink) | | |
| 包裝方式 (Packing) | | DRAWN | Chu8.. |
| Tied Hank | See Hank Detail | | |
| Carton Size | 480 x 320 x 250 | | |
| Pack Number | 125pcs/ UL Laster Labels | DATE | 08/29-2012 |
| Carton Print | See Purchase Order | | |
| TYPE | IEC 60320, C13 RA to ROJ(S&R) Power Supply Cord | | |
| DRAWNING NO. | 098MM983 | REV | A |

**CnC Tech, LLC**
Industrial Cable and Connector Technology

| | | | |
|---|---|---|---|
| CUSTOMER | CnC | | |
| P/N No. | 800-1603-2-SJT0-BL-00150 | | |
| MATERIAL | PVC | UNIT | ㎜ |
| Customer Approval | | | |

業務校閱：
品管校閱：

Downloaded from Arrow.com.