PART NAME	NON-METALLIC ENCLOSURE (STYLE D)	PART No.	NBD-10445 & NBD-10465 & NBD-15445

MATERIAL:

INDOOR VERSION

SOLID BODY & COVER ____ ABS/PC BLENDED PLASTIC
UL94-5VB FLAMMABILITY RATING

CLEAR COVER _____ POLYCARBONATE PLASTIC
UL94V-0 FLAMMABILITY RATING
UV STABILIZED

OUTDOOR VERSION

SOLID BODY & COVER ____ PBT/PC BLENDED PLASTIC
UL94-5VA FLAMMABILITY RATING
UV STABILIZED

FINISH:

BODY ____ LIGHT GRAY
COVER ____ LIGHT GRAY OR CLEAR

COVER INCLUDES GRAY POLY-URETHANE GASKET.

AIR AND MOISTURE VENTS, STAINLESS STEEL LOCKING HASP, PANEL MOUNTING RAILS, GALVANIZED STEEL INNER PANEL AND STAINLESS STEEL WALL MOUNTING BRACKETS ARE NOT INCLUDED, BUT CAN BE PURCHASED SEPARATELY.

INDUSTRY STANDARDS:

INDOOR VERSION
UL508 TYPE 1, 2, 4, 4X INDOOR, 12 & 13
NEMA TYPE 1, 2, 4, 4X, 12 & 13
IEC529-IP65

OUTDOOR VERSION
UL508 TYPE 1, 2, 4, 4X, 12 & 13
NEMA TYPE 1, 2, 4, 4X, 12 & 13
IEC529-IP65

NOTE: COVER ATTACHES WITH PHILLIPS DRIVE NON-METALLIC SCREWS. (NOT SHOWN)



VIEW LESS COVER

NOTE: ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE UNLESS OTHERWISE SPECIFIED

DIMENSIONS = INCHES [MILLIMETERS]

INDOOR VERSION PART NO.		OUTDOOR VERSION PART NO.	DIMENSIONS																			
SOLID COVER	CLEAR COVER	SOLID COVER	A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	S	T	U	V	W
NBD-10445	NBD-10465	NBD-15445	7.530	6.700	6.500	5.900	4.705	2.952	15.000	14.405	13.980	12.790	12.222	10.824	7.385	7.400	3.137	3.860	14.870	14.865	13.700	6.039
			[191]	[170]	[165]	[150]	[120]	[75]	[381]	[366]	[355]	[325]	[310]	[275]	[188]	[188]	[80]	[98]	[378]	[378]	[348]	[153]

Revised 26JUN07

Downloaded from Arrow.com.