

Data Sheet | Item Number: 859-403/000-006

Jumper; for jumper slot; 3-way; insulated; blue

<https://www.wago.com/859-403/000-006>



Color: ■ blue

Similar to illustration

Electrical data

Rated current	18 A
---------------	------

Physical data

Width	16 mm / 0.63 inches
Height	21.5 mm / 0.846 inches
Depth	2.5 mm / 0.098 inches

Material data

Color	blue
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.015 MJ
Weight	1.5 g

Commercial data

PU (SPU)	25 (25) pcs
Packaging type	Bag
Country of origin	DE
GTIN	4066966271973
Customs tariff number	85366990990

Product Classification	
UNSPSC	39121421
eCl@ss 10.0	27-14-11-40
eCl@ss 9.0	27-14-11-40
ETIM 9.0	EC002586
ETIM 10.0	EC002586
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 859-403/000-006	↓

Documentation

Bid Text			
859-403/000-006	19.02.2019	xml 2.53 KB	↓
859-403/000-006	20.02.2019	docx 13.56 KB	↓

CAD/CAE-Data													
<table border="1"> <thead> <tr> <th colspan="2">CAD data</th> </tr> </thead> <tbody> <tr> <td>2D/3D Models 859-403/000-006</td> <td>↓</td> </tr> </tbody> </table>	CAD data		2D/3D Models 859-403/000-006	↓	<table border="1"> <thead> <tr> <th colspan="2">CAE data</th> </tr> </thead> <tbody> <tr> <td>EPLAN Data Portal 859-403/000-006</td> <td>↓</td> </tr> <tr> <td>WSCAD Universe 859-403/000-006</td> <td>↓</td> </tr> <tr> <td>ZUKEN Portal 859-403/000-006</td> <td>↓</td> </tr> </tbody> </table>	CAE data		EPLAN Data Portal 859-403/000-006	↓	WSCAD Universe 859-403/000-006	↓	ZUKEN Portal 859-403/000-006	↓
CAD data													
2D/3D Models 859-403/000-006	↓												
CAE data													
EPLAN Data Portal 859-403/000-006	↓												
WSCAD Universe 859-403/000-006	↓												
ZUKEN Portal 859-403/000-006	↓												

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com