

USB-C to USB Micro-B Cable (M/M) - USB 3.2, Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 6 ft. (1.83 m)

MODEL NUMBER: U426-006



Connects a smartphone or other USB Micro-B device to your laptop, MacBook, Chromebook or Ultrabook's USB-C or Thunderbolt 3 port.

Features

USB-C to USB Micro-B Cable Connects a USB 3.0 Micro-B Device to Your Computer or Tablet This six-foot USB-C to Micro-B cable allows you to connect your smartphone, external hard drive or other device with a USB Micro-B port to any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks.

PD Charging Cable Charges Devices and Transfers Data at Fast USB 3.1 Gen 1 Speeds The USB-C to USB Micro-B cable supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. The Power Delivery cable also provides power output up to 3 amps (60 watts), which is more than sufficient for charging, syncing and powering compatible devices. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Specifications

OVERVIEW	
UPC Code	037332218384
Technology	Thunderbolt; USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)

Highlights

- USB-C to Micro-B cable compatible with USB Micro-B, USB-C and Thunderbolt 3 devices
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Power Delivery cable provides 3A (60W) power output for charging mobile devices
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

Applications

- Charge and sync a USB Micro-B mobile device from a USB-C vehicle charger or wall charger up to 6 ft. away
- Transfer data between an external hard drive and your laptop or computer

System Requirements

- Device with a USB-C or Thunderbolt 3 port (USB 3.1 Gen 1 compatibility required to achieve 5 Gbps speeds)
- Device with a USB Micro-B port (USB 3.0 compatibility required to achieve 5 Gbps speeds)

Package Includes

- U426-006 USB Type-C to USB Micro-B Cable, M/M, 6 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	USB 3.0 MICRO-B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5 mm
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.