



5.0

1 Review



5.0

1 Review

Need Help?

[Browse All Products](#) | [Cat5e / Cat6 / Cat6a](#) | [Cat5e](#) | [Cat5e Plenum Patch Cables](#)

Loading...

5ft Cat5e Non-Booted UTP Unshielded Ethernet Network Patch Cable - Plenum CMP-Rated - Gray

For network adapters, hubs, switches, routers, DSL/cable modems, patch panels and other high performance networking applications where plenum cables are required.



5.0

1 Review

Roll over image to zoom in

Product # : 15227

Connector 1 : (1) RJ-45 Male

Connector 2 : (1) RJ-45 Male

Colors :

Grey

Blue

Black

Lengths :

5ft

3ft

7ft

10ft

14ft

15ft

[+ show all lengths](#)

In Stock, only 2 left



Add



Need it shipped today?

Place your order before the timer runs out!

02: 52: 12

print share chat

Product Info

Customer Reviews

Questions & Answers

Distributors

More Choices

Description

Features

Certifications

Specs

Uses

Product Description

Strict building code requirements for cabling in plenum spaces have created installation challenges in settings such as schools, hospitals and other commercial buildings. C2G has expanded its connectivity portfolio to include a line of cables that are ideal for routing through plenum space above dropped ceilings or under raised floors.

Applications include voice/data/video distribution; this cable will handle bandwidth-intensive applications. Meets all Cat5E TIA/EIA standards, and reduces both impedance and structural return loss (SRL) .

Constructed from high quality plenum cable, this design minimizes Near-End Crosstalk (NEXT) levels. Available in Gray, Blue and Black to easily color-code your network installation.

Product Features

- Rated for Plenum, in-wall installations
- Cat5e cable with standard RJ45 connectors
- Available in lengths up to 100ft
- TAA Compliant



WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications

Downloaded from Arrow.com



Product Specifications

Color :	Grey
Length :	5.00 Foot
Jacket Rating :	Plenum
UPC :	757120152279
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.126 LB

- Connectors: 50 micron gold plated RJ45
- Wired: 568B
- Tested to 350MHz
- TIA-568-C.2
- RoHS Compliant

Product Uses

- 10Base-T
- 100Base-T
- 1000Base-T
- 155Mbps ATM
- 4/16Mbps Token Ring
- TP-PMD

Recently Viewed...



Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**
- [f](#) [t](#) [v](#) [b](#)

