HiPer-D® Contacts and Tools

#8 power contacts for combo HiPer-D® connectors

#8 POWER CONTACTS FOR COMBO HIPER-D CONNECTORS

These size #8 contacts snap into Glenair combo HiPer-D® size #8 cavities and can be removed with a plastic extraction tool. Crimp termination. Two sizes are available, #0812 for AWG 12-14 wire, and #0816 for AWG 16-18 wire. Gold plated copper alloy, 1000 VAC DWV rating, 23 amp current rating. Optional sealing boot prevents moisture ingress. ***Intermateable with standard D-Subminiature size #8 power contacts.***

Fig. 1
Pin Contact
850-056

Fig. 2
Socket Contact
850-057

Fig.	Contact Type	AWG Wire Size	Part Number Contact Only	Part Number Contact and Sealing Boot
1	Pin	#12, #14	850-056-0812	850-056-0812F
		#16, #18	850-056-0816	850-056-0816F
2	Socket	#12, #14	850-057-0812	850-057-0812F
		#16, #18	850-057-0816	850-057-0816F

Pin Contact
850-056-0812



Pin Contact
850-056-0816



Socket Contact
850-057-0812



Socket Contact
850-057-0816



Material and Finish

Contact: Copper alloy, 50 microinches gold over nickel.

Sealing Boot: Thermoplastic and Fluorosilicone

Specifications

Current Rating: 23 Amps
Contact Resistance: 10 milliohms
Crimp Tensile Strength: AS39029 Table 10
Temperature Range: -65° to + 200° C.

Tools

Crimp Tool: 859-081 (Daniels M309)
Positioner for Crimp Tool: 859-083 (Daniels TP1711
Insertion/Extraction Tool: 809-132 (M81969/14-04)

E

© 2015 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • Series 28 HiPer-D catalog
Dimensions in Inches (millimeters) are subject to change without notice.

Downloaded from Arrow.com.