D SUB IP 67 FE STR_PCB_9P_S4_METAL FRAME

Spotted an error? | Print page | Back

Image is for illustration purposes only. Please refer to product description.

Accessories

Combinables

Login to MyHARTING for pricing and stock check

Quantity: 50

Shopping cart

Email inquiry

Catalogue
HARTING Device Connectivity - Page 374

Browse

Download

- Features
- Connection data
- Dimensions and weight
- Supplements

Part number:	09 67 609 8775
Description:	D SUB IP 67 FE STR_PCB_9P_S4_METAL FRAME

Features

Application:	Board Connector Panel Mount
Class of Protection:	IP67
Gender:	Turned Female Contact
Mating Hardware:	Flange Thread M3
No. of contacts:	9
Performance level:	S4
RoHS conformity:	Yes
Termination Type:	Solder
Type:	Rear Mount Straight Metal Frame

Top

Connection data

Current:	5 A @ 20°C

Top

Dimensions and weight

Net Weight:	78.5 g

Top

Supplementals

Series:	D-Sub Waterproof

Top

Downloads

Title	Download
HARTING Device Connectivity - Page 374	PDF

Accessories

Image	Part number	Description	Tech. info	Quantity
	09 67 002 9050	D SUB IP 67 SHIELDED CAP_MA_9p_4-40 UNC		1 Shopping cart
	09 67 002 9055	D SUB IP 67 SHIELDED CAP_MA_9p_M3		1 Shopping cart
	09 67 002 9006	FEMALE SCREW LOCK M3		1 Shopping cart

Combinables

Image	Part number	Description	Tech. info	Quantity
	09 67 409 5615	D-Sub male solder cup 9-pole IP67		1 Shopping cart

Recently viewed - Delete

D SUB IP 67 FE ANG_PCB_09P_S4_ME FRAM

Show product details

D SUB IP 67 MA STR_PCB_9P_S4_META FRAME

Show product details

D SUB IP 67 MA ANG_PCB_9P_S4_MET FRAME

Show product details

D SUB IP 67 FE STR_PCB_9P_S4_META FRAME

Show product details

D SUB IP 67 FE ANG_PCB_9P_S4_MET FRAME

Show product details

DSUB SV FE SSDP ANG87-254 50P AU2

Show product details

DSUB SV MA SSDP STR 50P AU3

Show product details

DSUB SV MA SSDP STR 50P AU2

Show product details

DSUB SV FE SSDP STR 50P AU3

Show product details

DSUB SV MA SSDP ANG36-254 25P AU3

Show product details

Recently searched

No searches have been done yet.

Downloaded from Arrow.com.