Data Sheet | Item Number: 756-3201/120-050
Connecting cable; 12-pole; Length: 5 m
https://www.wago.com/756-3201/120-050


DISCONTINUED:
01.01.2027




Pin 9, 11, 12: 1.00 mm²;
Pin 1 - 8: 0.34 mm²

1	white	9	blue
2	green	10	commoned with 9
3	yellow	11	brown
4	gray	12	green/yellow
5	pink		
6	red		
7	black		
8	violet		

Color: ■ black





Dimensions in mm

Technical data	
Connection type	M23 socket - free end
Pole number	12
Cable connection direction to mating direction	0 °
Cable length	5 m
Operating voltage	≤ 300 V
Operating current	8 A
Rated impulse withstand voltage	≥ 2.0 kV rms

Downloaded from Arrow.com.

Mechanical data

Bending cycles	2 million
Drag chain capability	Yes
Weight	522 g
Color	black

Environmental requirements

Ambient (operating) temperature (dynamic)	-25 … +80 °C
Ambient (operating) temperature (static)	-40 … +90 °C
Protection type	IP67

Commercial data

Product Group	23 (I/O passive and accessories)
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918568883
Customs tariff number	85444290900
End of Sale	2027-01-01
End of Production	2027-01-02
End of Delivery	2027-03-01
End of Service and Repair	2027-07-01

Product Classification

UNSPSC	26121629
eCl@ss 10.0	27-06-03-11
eCl@ss 9.0	27-06-03-11
ETIM 9.0	EC001855
ETIM 10.0	EC001855
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 756-3201/120-050

Downloaded from Arrow.com.

Documentation

System Description

Sensor/Actuator Boxes – General Product Information	pdf 428.34 KB	

CAD/CAE-Data

CAE data

WSCAD Universe 756-3201/120-050	

Downloaded from Arrow.com.