

RIHE-1611-N/P-IN-24VAC/DC



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → PLC Wiring Systems
→ PLC Decoupling Interfaces

General Information

Extended Product Type:	RIHE-1611-N/P-IN-24VAC/DC
Product ID:	1SNA020956R2100
EAN:	3472590209564
Catalog Description:	RIHE-1611-N/P-IN-24VAC/DC - Decoupling Interface
Long Description:	RIHE 16N/P relay 1NO 5 A input interface 24 V AC/DC for HE10/20.

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85371098

Popular Downloads

Data Sheet, Technical Information:	1SNC127006C0202
Instructions and Manuals:	1SNC127006C0202

Dimensions

Product Net Width:	165 mm
Product Net Height:	75 mm
Product Net Depth / Length:	65 mm
Product Net Weight:	0.208 kg

Technical

Connection Type:	Pluggable - Screw clamp
Pollution Degree:	2
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	7.5 mm
Recommended Screw Driver:	3.5 mm

Technical UL/CSA

Connecting Capacity UL/CSA:	Stranded 14 AWG
Flammability According to UL94:	V0

Certificates and Declarations (Document Number)

cUL Certificate:	1SND117003A0201
-------------------------	-----------------

Declaration of Conformity - CE: 1SND225028U1000

Environmental Information: 1SNC127006C0202

Instructions and Manuals: 1SNC127006C0202

Classifications

Object Classification Code: K

ETIM 4: EC001437 - Switching relay

ETIM 5: EC001437 - Switching relay

ETIM 6: EC001437 - Switching relay

Container Information

Package Level 1 Units: 1 piece

Package Level 1 Width: 135 mm

Package Level 1 Depth / Length: 175 mm

Package Level 1 Height: 74 mm

Package Level 1 Gross Weight: 0.208 kg

Package Level 1 EAN: 3472590209564

Package Level 2 Units: 16 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 500 mm

Package Level 2 Height: 300 mm

Package Level 3 Units: 384 piece

Product Packing Type: Box

