

- Products

Barcode Scanners

Handheld Barcode Scanner

Industrial Barcode Scanner

Wireless Barcode Scanner

Hands-Free Barcode Scanner

Healthcare Barcode Scanner

In-Counter Scanner

2D Barcode Scanner

Mobile Computers

Wearable Scanner and Mobile Computer

Enterprise Sleds For Apple Devices

Vehicle Mount Computers

Printers and Media

Wireless Infrastructure

OEM Scanner

Software

Vocollect Voice Solutions

Retired Products

Support Services

How To Buy



Previous

Next

Granit 1911i Wireless Industrial-Grade Area-Imaging Scanner

The Granit™ 1911i wireless industrial-grade area-imaging scanner is designed to withstand the varied demands that exist in harsh working environments. Featuring a custom built housing that is redefining the standard for scanner reliability, the IP65 rated Granit 1911i is built to survive 5,000 3.3’ (1 m) tumbles and 50 drops to concrete from 6.5’ (2 m) even at -4°F (-20°C). As a result, businesses can expect to experience minimal device downtime and a lower overall cost of ownership.

Click Here for Granit Product Tour

- Features and Benefits
- Accessories
- Documents
- Software
- Links
- Related Products

Granit 1911i Wireless Industrial-Grade Area-Imaging Scanner Accessories

STANDS/HOLDERS/CORDLESS BASES/ACCESS POINTS

AP-100BT-07N: Access Pont Class 1 Bluetooth, 100m (300’), up to 7 scanners can be connected RS232/USB/KBW (cables sold separately)

CCB02-100BT-07N Base: charging, Class 1 Bluetooth, 100m (300’), up to 7 scanners can be connected, RS232/USB/KBW host interfaces (cable sold separately)

COB02 Base: Charge-Only only 1 scanner can be charged at a time, power supply must be purchased separately

HOLDER-010-U Holder: desktop/wall mount (include mounting hardware)

STND-30R00-011-4 Stand: gray, 30cm (12”) height, rigid rod, weighted base, Granit cradle

STND-33F00-012-4 Stand: gray, 33cm (13”) height, flexible rod, weighted base, Granit cup

VMHOLDERK Vehicle Mount Kit: contains vehicle mount forked holder (VM Holder), adjustable arm with ball joints (ADJARME) and mounting hardware

ACCESSORIES - CABLES

CBL-020-300-C00 Cable: RS232 (+/-5V signals), black, DB9 Female, 3m (9.8’), coiled, 5V external power with option for host power on pin 9

CBL-120-300-C00 Cable: RS232C (+/-12V signals), black, DB9 Female, 3m (9.8’), coiled, 5V external power with option for host power on pin 9

CBL-320-300-C00 Cable: RS232 (+/-12V signals), black, DB9 Male, 3m (9.8’), coiled, external power with option for host power on pin 9

CBL-500-300-C00 Cable: USB, black, Type A, 3m (9.8’), coiled, 5V host power

CBL-500-300-S00 Cable: USB, black, Type A, 3m (9.8’), straight, 5V host power

CBL-500-300-S00-01 Cable:USB, black, Type A, 3m (9.8’), straight, 5v host power, industrial grade

CBL-500-500-C00 Cable: USB, black, Type A, 5m (16.4’), coiled, 5V host power

CBL-503-300-C00 Cable: USB, black, 12V locking, 3m (9.8’), coiled, 5V host power

CBL-503-300-S00 Cable: Cable: USB, black, 12V locking, 3m (9.8’), straight, 5V host power

CBL-503-500-C00 Cable: USB, black, 12V locking, 5m (16.4’), coiled, 5V host power

CBL-720-300-C00 Cable: KBW, black, PS2, 3m (9.8’), coiled, 5V external power with option for host power

ACCESSORIES - CHARGERS

MB4-BAT-SCN01NADO Charger: 4-bay battery charger (NA) for use with Voyager 1202g, Xenon 1902, 3820, 3820i, 4820, 4820i, & 1911i Lithium-ion batteries, NA desktop power supply (PS-050-4000D-NA), two mounting screws (100006897), and instructions (MBC-INST)

MB4-BAT-SCN01NAW0 Charger: 4-bay battery charger (NA) for use with Voyager 1202g, Xenon 1902, 3820, 3820i, 4820 & 4820i Lithium-ion batteries, NA wallmount power supply (PS-050-4000W-NA), two mounting screws (100006897), and Instructions (MBC-INST)

ACCESSORIES - HOLDERS/MISCELLANEOUS

HOLSTER-INDUSTRIAL:When clipped to a user’s belt holster enables storage of Granit 1911i cordless image while leaving hands-free to accomplish other tasks (scanner sold separately)

TOOLBAL Miscellaneous:Miscellaneous: Take up reel/balancer

PRODUCTS

Barcode Scanners

Mobile Computers

Enterprise Sleds for Apple Devices

Wearable Scanner and Mobile Computer

Vehicle Mount Computer

Wireless Infracstructure

OEM Scanner

Software

Retired Products

INDUSTRIES

Collection & Delivery

Healthcare

Field Workforce

Ports & Intermodal

Postal

Retail

Warehouse

CONTACT / SUPPORT

Contact Us

How to Buy

Technical Support

Service & Repair

Service & Contracts

[Feedback](#)

NEWSROOM

Facebook

Twitter

LinkedIn

Press Releases

Video Center

LEGAL

Terms & Conditions

Privacy Statement

Site Map

Patents

ICP 15008415-23