Part Number : 192110005
Product Description : Krimptite Wire Pin Terminal for 16-14 AWG Wire, Bag
Series Number : 19211
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : WP-1614
Packaging Alternative : 192110006 (Adhesive Tape on Reel)



Documents and Resources

Drawings

192110005_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19211
Description	Krimptite Wire Pin Terminal for 16-14 AWG Wire, Bag
Application	Power, Wire-to-Component
Comments	Pin Length 9.40mm
Product Name	Wire Pin,Krimptite
UPC	800755062052

Agency

CSA	LR18689
UL	E32244

Physical

Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.626/g
Packaging Type	Bag
Plating min - Mating	1.016µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.26mm max.
Wire Size (AWG)	14, 16
Wire Size mm^2	N/A

Downloaded from Arrow.com.

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm² - 0.5mm²	640030100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

Downloaded from Arrow.com.