

Sign in for a personalized NXP experience.

LPC55S69JEV59

ACTIVE

OverviewOperating FeaturesEnvironmentalQualityShipping

BUY OPTIONS



Image not available

Package

VFBGA59: VFBGA59, very thin fine-pitch ball grid array package, 59 terminals, 0.4 mm pitch, 4 mm x 4 mm x 0.77 mm body

LPC55S69JEV59E - ACTIVE

12NC: 935462189551

Details

- Packing:** TRAY-Tray, Bakeable, Single in Drypack
- Min. Package Quantity:** 490
- Min. Order Quantity:** 490
- Lead Time:** 18 weeks
- Budgetary Price:** 10K at \$3.07 USD

Order

[Order from distributors](#)

> [Order from distributors](#)

LPC55S69JEV59Y - ACTIVE

12NC: 935462189518

Details

- Packing:** REEL-Reel 13" Q1/T1 in Drypack
- Min. Package Quantity:** 3000
- Min. Order Quantity:** 3000
- Lead Time:** 18 weeks
- Budgetary Price:** 10K at \$3.07 USD

Order

[Order from distributors](#)

> [Order from distributors](#)

Operating Features

No information available

Environmental

Part/12NC	PbFree	EU RoHS	Halogen Free	RHF Indicator	REACH SVHC	Weight (mg)
LPC55S69JEV59E (935462189551)	Yes	Yes Certificate Of Analysis (CoA)	Yes	D	REACH SVHC	27.9177013641079
LPC55S69JEV59Y (935462189518)	Yes	Yes Certificate Of Analysis (CoA)	Yes	D	REACH SVHC	27.9177013641079

Quality

Part/12NC	Safe Assure Functional Safety	Moisture Sensitivity Level (MSL)	Peak Package Body Temperature (PPT) (C°)		
		Lead Free Soldering	Lead Soldering	Lead Free Soldering	
LPC55S69JEV59E (935462189551)	No	3	240	260	
LPC55S69JEV59Y (935462189518)	No	3	240	260	

Shipping

Part/12NC	Harmonized Tariff (US) Disclaimer	Export Control Classification Number (US)
LPC55S69JEV59E (935462189551)	854231	5A992C
LPC55S69JEV59Y (935462189518)	854231	5A992C

News Nov 4, 2024 | NXP Semiconductors Reports Third Quarter 2024 Results [Read More](#)



ABOUT NXP CAREERS INVESTORS MEDIA CONTACT MY NXP ACCOUNT BENEFITS



Privacy | Terms of Use | Terms of Sale | Accessibility | Website Feedback

©2006–2025 NXP Semiconductors. All rights reserved.