


**Data Sheet | Item Number: 211-112**

Nozzles; Length: 12 mm; only for use with 211-110/-111/-120/-121; halogen-free;  
Cable outer diameter: 1.6 ... 3.2 mm; black

<https://www.wago.com/211-112>



Color: ■ black

| Technical data                  |  |                                                     |
|---------------------------------|--|-----------------------------------------------------|
| Suitable                        |  | for wire diameter 1.6 ... 3.2 mm or 0.25 ... 1.5 mm |
| Delivery form                   |  | Component                                           |
| Properties                      |  | 12 mm long; for one marker                          |
| Printing device                 |  | TP 298+                                             |
| Physical data                   |  |                                                     |
| Length                          |  | 12 mm                                               |
| Mechanical data                 |  |                                                     |
| Mounting type                   |  | Sliding on conductor                                |
| Material data                   |  |                                                     |
| Color                           |  | black                                               |
| Material                        |  | Polyurethane                                        |
| Adhesive information            |  | without adhesive                                    |
| Halogen-free                    |  | Yes                                                 |
| Weight                          |  | 0.2 g                                               |
| Fire load                       |  | 0 MJ                                                |
| Environmental requirements      |  |                                                     |
| Ambient temperature (storage)   |  | +10 ... +25 °C                                      |
| Ambient temperature (operation) |  | -40 ... +100 °C                                     |
| Relative humidity               |  | 40 ... 60 %                                         |



| Commercial data       |                                |
|-----------------------|--------------------------------|
| Product Group         | 2 (Terminal Block Accessories) |
| PU (SPU)              | 2000 pcs                       |
| Packaging type        | Box                            |
| Country of origin     | DE                             |
| GTIN                  | 4045454486051                  |
| Customs tariff number | 39269097900                    |

| Product Classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 39121722             |
| eCl@ss 10.0            | 27-40-04-01          |
| eCl@ss 9.0             | 27-40-04-01          |
| ETIM 9.0               | EC001530             |
| ETIM 8.0               | EC001530             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                        |
|----------------------------------|------------------------|
| RoHS Compliance Status           | Compliant,No Exemption |

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 211-112

↓

| 1 Compatible Products    |
|--------------------------|
| 1.1 Required Accessories |
| 1.1.1 Marking            |
| 1.1.1.1 Marker           |



[Item No.: 211-111](#)  
Marker; for TP printers; for use in nozzles;  
Length: 12 mm; white