




1-1478075-0 Product Details

Share Print Email



Active

BNC RF Connectors

BNC R/A Plg Hex 500hm Silver Pltd RG58C/

1-1478075-0

TE Internal Number: 1-1478075-0

Product Highlights View All

- Connector - RF
- Plug
- Connector Style = Plug
- Applies To Coaxial Cable
- Coaxial Cable Termination Type = Crimp

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through
Distributor

Feedback

Documents Features Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector - RF
Gender	Plug
Grade	Professional
Sealed	No
Isolated	No
Dielectric Material	PTFE
Coupling Nut Material	Brass

Mechanical Attachment	
Surface Mountable	No
Hardware Included	No
Panel Mount Retention	Without
Hand Tool No.	9-1478240-0
Interchangeable Die Set Number	9-1478242-0

Electrical Characteristics	
Connector Impedance (Ω)	50
Frequency	DC - 4 GHz

Termination Features	
Coaxial Cable Termination Type	Crimp
Crimp Type	Hex
Crimp Dimensions	1.75 + 2.6 + 5.6 + 6.5

Body Features	
Body Style	Elbow
Body Material	Brass
Body Plating	Silver
Polarized	No
Ferrule Type	Hex
Gasket Material	White Silicone Rubber

Contact Features	
Center Contact Material	Brass
Center Contact Plating	Silver

Housing Features	
Connector Style	Plug

Configuration Features	
Coaxial Cable Type (RG/U or Mfg.)	141A, 58C, Raychem 5021D1331, Raychem 5021D1831, Raychem 5021M1631, Raychem EPD 71169Q, URM 43, URM 76
Number of Ports	1

Industry Standards	
Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Converted to comply with RoHS directive
Military Style Number	UG-1812/U

Environmental	
Operating Temperature (Max.) (°C)	165

Conditions for Usage	
Applies To	Coaxial Cable

Packaging Features	
Packaging Method	Individual
Packaging Quantity	50

Other	
Brand	Greenpar

Related Products

Not quite the product
you're looking for?
Find Similar Products

**View Part in Product
Feature Selector**

Check for Tooling

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

