



SCHROFF

Project - 0 item(s)

MY PROJECT LIST

PRODUCTS

APPLICATIONS

INDUSTRIES

NEW PRODUCTS

CONFIGURATORS

Products ▾

Search



Home > Type H-VT heavy duty, recessed mounting



Type H-VT heavy duty, recessed mounting

SCHROFF



Other Views

**Catalog Number: 34560-742**[Back To Product](#)

- Mounting top and bottom
- Al extrusion, anodised finish, conductive contact surface, with HP markings
- For direct backplane mounting
- Recessed installation for high mechanical demands (H-VT)
- < 28 HP not printed

Product family:

- EuropacPRO
- RatiopacPRO
- PropacPRO
- CompacPRO

Note:

Delivery is in standard pack multiples. Pricing is per individual item

Type:

Individual Components

Individual Component Type:

Horizontal Rails & Accessories

Standard pack quantity (SPQ):

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

**Select product specifications before modifying or adding to project list or requesting a quote.**

Length-mm-defining

218.44

[Clear Selection](#)Quantity [Add Item to Project List +](#)**Documents**

Shock and vibration test according to IEC 48/IEC 61587



Shock and vibration test according to Deutsche Bundesbahn standards



Seismic test

Links




Native CAD files

Technical Data

Length mm	218.44
Qty	1 piece (SPQ 10)
Delivery is exclusively made in Standard Pack Quantity (SPQ)	10
Material	Aluminium extrusion
Finish	Anodised, conductive contact surfaces
Description	Horizontal rail

Item	Quantity	Description
1	1	Horizontal rail, aluminium extrusion, anodised, conductive contact surfaces

Accessories

	EMC gasket kit between horizontal rail and horizontal rail	24562-542	Add Item to Project List +
	Countersunk screw, torx (M4×10), steel zinc plated, PU 100 pieces	24560-155	Add Item to Project List +
	Countersunk screw, torx (M4×14), steel zinc plated, PU 100 pieces	24560-130	Add Item to Project List +

EXPLORE	CONTACT	DOWNLOAD
About Us	Customer Service	Download Center
Services & Capabilities	Find a Sales Office or Distributor	Reference Projects
News & Events	Global Locations	Videos
Newsletter Subscriptions	Product Compliance & Certifications	Product Configurators
Strategic Partnerships	Partner Login	Warranties and Terms of Sale & Procurement
Investor Relations		

Connect With Us

