



PC-Board layout
view component side
thickness 1,6 mm





Connector retention and insertion forces on PC-Board: 25 N / 80 N

Part number	Screw lock thread	Performance level
09 66 353 3633	M3	PL1
09 66 353 6633	M3	PL2
09 66 353 7633	M3	PL3
09 66 353 3613	4-40 UNC	PL1
09 66 353 6613	4-40 UNC	PL2
09 66 353 7613	4-40 UNC	PL3

All Dimensions in mm
Original Size DIN A4

All rights reserved

Department EC PD - FR

HARTING Electronics GmbH
D-32339 Espelkamp

Scale	Free size tol.	Ref.
1:1		Sub.

Created by	Inspected by	Standardisation	Date	State
SONN	BAGDIKIAN	HOFFMANN	2014-10-16	Final Release

Title: D-Sub 25-Pole Female Angled

Doc-Key / ECM-Nr.: 100597692/UGD/000/A 500000080782

Type: TB | Number: 0966353X6X3 | Rev.: A | Page: 1/1

Downloaded from Arrow.com.

A4