

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 48U, Shock Packaging, 2000 lbs, Black, 2258H x 600W x 1070D mm

AR3107SP

## Overview

### Presentation

NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 2000 lbs (907 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).

### Lead time

Usually Ships within 6 Weeks

## Main

### Product or component type

Rack enclosure

### Number of rack unit

48U

### Provided equipment

Baying hardware  
Documentation CD  
Key(s)  
Keyed-alike doors and side panels  
Leveling feet  
Mounting hardware  
Pre-installed casters  
Side panels

## Physical

### Height

225.8 cm

### Width

60 cm

### Depth

107 cm

### Net weight

138.23 kg

### Colour

Black

### Mounting preference

No preference

### Mounting mode

Not rack-mountable

### Maximum mounting depth

91.49 cm

### Minimum mounting depth

19.1 cm

### Rack width

19"

### Marking

14 gauge EIA mounting rail  
16 gauge front door  
16 gauge post  
18 gauge rear door  
18 gauge roof  
18 gauge side panels

### Permanent permissible load

1020.6 kg dynamic  
1701.0 kg static

## Conformance

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

<b>Standards</b>	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	245.1 cm
<b>Package 1 Width</b>	132.1 cm
<b>Package 1 Length</b>	110.5 cm
<b>Package 1 Weight</b>	240.86 kg

## Contractual warranty

---

<b>Warranty</b>	5 year repair or replace
-----------------	--------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Reach Free Of Svhc

 Toxic Heavy Metal Free

 Mercury Free

 RoHS Exemption Information Yes

## Certifications & Standards

### Reach Regulation

[REACH Declaration](#)

### Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

### Environmental Disclosure

[Product Environmental Profile](#)

### Circularity Profile

[End of Life Information](#)

Image of product / Alternate images

Alternative

---





